





Datenblatt



RECOMMENDED P.C.B LAYOUT



MATERIAL

HOUSING : NYLON 6T,UL94V-0
CONTACT : COPPER ALLOYS
PLATED : GOLD-FLASH
COLOR : BLACK

SPECIFICATION

CURRENT: 1A
OPERATING TEMPERATURE: -55°C TO $+105^{\circ}\text{C}$
CONTACT RESISTANCE : 20 MILLIOHMS MAX
INSULATION RESISTANCE : 5000 MEGAOHMS MIN
DIELECTRIC STRENGTH : 1000 VAC MIN

A: 8.20 mm B: 4.00 mm C: 2.70 mm