





Datenblatt



A: 10.84 mm; B: 5.80 mm; C: 2.50 mm



NOTES:

1. HOUSING: PBT, UL-94V0
COLOR : BLACK
2. CONTACT: BRASS
PLATED : GOLD FLASH
3. CURRENT : 3A
4. OPERATING TEMPERAURE : -55° C TO +105° C
5. CONTACT RESISTANCE : 20 MILLIOHMS MAX
6. INSULATION RESISTANCE: 1000 MEGAOHMS MIN
7. WITHSTAND VOLTAGE : 500 V AC MIN