




Datenblatt



A: 12,64 mm; B: 6,80 mm; C: 3,30 mm



NOTES:

1. HOUSING: PBT, UL-94V0
COLOR : BLACK
2. CONTACT: BRASS
PLATED : GOLD FLASH
3. CURRENT : 3A
4. OPERATING TEMPERATURE : -55° C TO +105° C
5. CONTACT RESISTANCE : 20 MILLIOHMS MAX
6. INSULATION RESISTANCE: 1000 MEGAOHMS MIN
7. WITHSTAND VOLTAGE : 500 V AC MIN