


Tough TG-6

**OLYMPUS**

# BUILT FOR ADVENTURE



Available Colors:



Red Black

**F2.0**

HIGH-SPEED LENS

**8X ZOOM**

WITH DIGITAL TELECONVERTER

**50 FT**

15M WATERPROOF

**CUSTOM MODES**

MACRO & UNDERWATER

**4K**

ULTRA HD VIDEO

## Key Features:

- Bright F2.0 high-speed lens
- High-Speed Image Sensor features improved dynamic range and noise reduction in low-light conditions
- TruePic™ VIII Image Processor powers blazing continuous shooting speeds, up to 20 fps in full resolution RAW
- Waterproof: 50 ft (15 m), Crushproof: 220 lbf (100 kgf), Shockproof: 7 ft (2.1 m), Freezeproof: 14°F (-10° C), Dustproof
- Hermetically sealed Anti-fog prevents lens fogging while Anti-reflective coating minimizes ghosts and flares
- 2x Digital Teleconverter provides a maximum of 8x zoom when combined with the 4x optical zoom
- Variable Macro System with 4 modes including Microscope, Microscope Control, Focus Stacking, and Focus Bracketing. Shoot as close as 1cm in Program, Aperture and Macro Modes
- Advanced Underwater Modes include Macro, Microscope, Wide, Snapshot, HDR, and 3 White Balance Modes (Shallow, Mid-Range, Deep)
- Versatile shooting modes include RAW Capture, Live Composite, PRO Capture Mode, and Ultra HD 4K Video
- Action Track Sensors capture and log environmental data with built-in GPS, compass, temperature sensor, and manometer/barometer
- Date Imprint records date and time when shooting stills for quick reference and record keeping
- Built-in Wi-Fi syncs to a smartphone device for remote shooting and sharing
- New accessories include LB-T01 Lens Barrier, PT-059 Underwater Housing, FCON-T02 Circular Fisheye Converter, and CSCH-127

[getolympus.com](http://getolympus.com)