

BEYON

ENGLISH

BEYON wireless button 1Y.13.Bxx

VFRSIONS

1Y.13.B10: 2 Channel, White

1Y.13.B12: 2 Channel, Black

1Y.13.B20: 4 Channel, White

1Y.13.B22: 4 Channel, Black

TRANSMISSION RANGE

- Transmission range: approximately 10 m in free space and without obstacles
- The transmission range may vary depending on the building structure

Example:

- Reinforced concrete walls and/or metal walls
- Button mounted on a metal surface or in metal frames
- Partition walls filled with insulating wool on a metallic backing
- Ceilings with metal or carbon fiber panels
- Lead glass or glass with metal cladding, steel furniture

TECHNICAL SPECIFICATIONS

Source of energy	Integral self powered generator
Operating frequency	2.4 Ghz Bluetooth BLE
Approvals	2.4 Ghz: CE, FCC, IC (Europe, US, Canada)
Switching cycles	min. 50 000
Operating temperature	−25°C +65°C

Information

- The BEYON button is intended for internal use
- The product is not suitable for environments with high vibration, mechanical shock, very high humidity, very dusty or in an explosive atmosphere

Safety instructions

- Choking hazard! Do not leave packaging material around.
- The children could swallow the smaller parts and choke
- Install and use the product according to this manual and do not modify the product in any way
- Improper cleaning can damage the product.
 - We recommend cleaning with a soft and damp cloth





