

## General product information

Standards	LVD
Approved for outdoor use	No
Article Description (max length 60 characters)	Battery adapter, Dx4, 6V E-transformer IP20 indoor
EAN (13 characters)	7318305184008
Colour (product)	White
Market introduction (year)	2018
Colour (light source)	N/A
Text in catalog	Battery eliminator, 6V, replaces 4xD batteries. White cable.
Catalog Page	552
Country of origin	China
Material (product)	Plastic
Customs Code	85044082 Battery adapter
Status (Movex)	20
Plug type	EUR
Cord length (cm)	300
Battery included	Yes
Battery Size	LR20/D (1,5V)
Power source	Transformer
Number of batteries	4
Transformer voltage	6V
Transformer effect	2,4W
Effect (W)	NA
Effect (W) per light source	NA
LED effects	No
Light sensor	No
Multi function	No
Timer control	No
Colour of cable	White
Dimmable	No
Dimmer included	N/A

Energy class	N/A
IP Class (Product)	IP20
IP Class (Transformer)	IP20
Kelvin	NA
Lumen	NA
Type of switch	No
Type of cord	PVC
IsolatedImage1	5184-000.I.1.0.jpg
Socket	N/A
Light source	N/A
ProductImage	5184-000.P.1.0.jpg
Height of consumer package	5
Height of transport package	32
Length of consumer package	24
Length of transport package	50
Quantity in transport package	20
Width of consumer package	12
Width of transport package	13,5
Gross Weight (Movex) (max 6 numbers and 3 decimals)	0.33
Net weight (max 6 numbers and 3 decimals)	0.185
Transport package weight	6.6
Consumer package weight	0.33
Transport package volume (dm3)	22
Consumer package volume (dm3) (max 6 numbers and 3 decimals)	1.08
ECommerce Sub Category	n/a
ECommerce Top Category	Accessories
Web category	270 Accessories
Web family	2702 Accessories
Warehouse Count DE	675
Warehouse count GKS	535