

## Product information

# 00 21 06 HK S

## "Tool Case ""BIG Basic Move"" Plumbing"

31 parts



- Equipped with four KNIPEX tools, a total of 31 brand tools, partly VDE-tested according to DIN EN 60900
- With a total of 54 inserting options
- Max. payload: 20 kg
- Volume: 33 litres
- Strong, ergonomic handle
- Heavy duty ABS material, black
- Circumferential aluminium frame
- Metal hinges
- Document compartment in the cover
- Two removable tool boards made of dirt-repellent PP twin-fall sheets with 31 tool pockets
- First tool board with ten tool pockets and an elastic strap on the cover side and eleven narrow and one large tool pocket on the base side
- Second tool board with ten tool pockets and an elastic strap on the base side and a document compartment on the cover side
- Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 14 large tool pockets
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Two metall tilting locks and three-digit combination lock for secure closing of the lid
- Label field with two stickers for individual labelling



### General

|                 |                       |
|-----------------|-----------------------|
| Article No.     | 00 21 06 HK S         |
| EAN             | 4003773084266         |
| Weight          | 10,855 g              |
| Dimensions      | 264 x 436 mm          |
| REACH compliant | does not contain SVHC |
| RoHS compliant  | not applicable        |

### Technical details

|                                         |                 |
|-----------------------------------------|-----------------|
| Dimension exterior (interior) width mm  | 430 mm (350 mm) |
| Dimension exterior (interior) height mm | 280 mm (200 mm) |
| Dimension exterior (interior) depth mm  | 515 mm (480 mm) |

### Content

|            |                                                                                                                                                                                                                       |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 86 03 250  | 1 x Pliers Wrench pliers and a wrench in a single tool (250 mm)<br>                                                                |
| 88 01 250  | 1 x KNIPEX Alligator® Water Pump Pliers (250 mm)<br>                                                                               |
| 88 01 300  | 1 x KNIPEX Alligator® Water Pump Pliers (300 mm)<br>                                                                               |
| 70 06 160  | 1 x Knipex Diagonal Cutter (160 mm)<br> 1000 V  |
| 306125     | 1 x Haunstetter PUK® Junior Hacksaw (150 x 240 mm)                                                                                                                                                                    |
| 1664000000 | 1 x Heyco Cutter (18 mm)                                                                                                                                                                                              |
| 90958      | 1 x Heyco Express key ( M 10)                                                                                                                                                                                         |

## Content

|            |                                                                                              |
|------------|----------------------------------------------------------------------------------------------|
| 75040-015  | 1 x Picard Flat brush (40 mm)                                                                |
| 75060-005  | 1 x Picard steel wire brush, 5-row (280 mm)                                                  |
| 75063-000  | 1 x Picard Plaster bowl (127 x 94)                                                           |
| 75075-040  | 1 x Picard Painter's spatula 40 mm, wood, high quality (40 mm)                               |
| 361 252 1  | 1 x Rennsteig Electrician's Chisel (250 x 10 mm)                                             |
| 3003010119 | 1 x Ruthe Locksmith's hammer, 300 g (300 g)                                                  |
| 15212      | 1 x Stabila Carpenter's pencil                                                               |
| 2281       | 1 x Stabila spirit level type 70 (30 cm)                                                     |
| L240 00055 | 1 x Stabila Folding ruler Stabila series 400 (200 mm)                                        |
| 0022086    | 1 x Wera set of hex key wrenches (1,5 - 10 mm)<br>○                                          |
| 031582     | 1 x Wera Screwdrivers for slotted screws 1160 i (0,6 x 3,5 x 100 mm)<br>⚡ 1000V ⚡            |
| 031587     | 1 x Wera Screwdrivers for slotted screws 1160 i (1,0 x 5,5 x 125 mm)<br>⚡ 1000V ⚡            |
| 031588     | 1 x Wera Screwdrivers for slotted screws 1160 i (1,2 x 6,5 x 150 mm)<br>⚡ 1000V ⚡            |
| 031601     | 1 x Wera Screwdrivers for cross recessed Phillips® screws 1162 i (PH1 x 80 mm)<br>⚡ 1000V ⚡  |
| 031603     | 1 x Wera Screwdrivers for cross recessed Phillips® screws 1162 i (PH2 x 100 mm)<br>⚡ 1000V ⚡ |
| 6135-0     | 1 x Zenten Pipe cutter (3 - 35 mm / 1/8 - 1 1/2")                                            |

## Accessories

|             |                                   |
|-------------|-----------------------------------|
| 00 21 06 LE | Tool Case "BIG Basic Move" empty, |
|-------------|-----------------------------------|

technical change and errors excepted



