Product information

98 99 15

Toolbox "BIG Twin Move RED" Electric Competence

42 parts



- Hard-wearing ABS material construction, red; equipped with a range of KNIPEX tools for working on systems, tested according to DIN EN/IEC 60900
- With a total of 95 inserting options
- Max. payload: 30 kg
- Volume: 38 litres

- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Free-standing in all opening positions thanks to snap-in cover holders with hinge mechanism on both sides, angle freely adjustable
- Can be opened from one or both sides; bottom and lid can be opened independently of each other
- Label field with two stickers for individual labelling
- Circumferential aluminium frame with securely mounted, sturdy centre wall that can be fitted on both sides, with versatile inserting options due to elasticated loops and twelve small pockets
- Metal hinges
- Three-digit combination lock for secure locking of the case
- Two metal tilt locks each for fixing the cover and the base
- Removable document compartment and removable tool board made from dirt-repelling twin-wall PP sheets with 13 tool pockets
- Base tray, can be fixed by press button, height 58 mm, can be subdivided by flexible inserts; cover plate with six large compartments
- Dimensions, exterior (W x H x D): 520 x 435 x 290 mm; dimensions, interior (W x H x D): 490 x 370 x 110/100 mm
- IEC 60900, DIN EN 60900

General	
Article No.	98 99 15
EAN	4003773084341
Weight	15,095 g
Dimensions	290 x 432 x 317 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Dimension exterior (interior) width mm	520 mm (490 mm)
Dimension exterior (interior) height mm	435 mm (370 mm)
Dimension exterior (interior) depth mm	290 mm (110 mm)

Content	
08 26 145	1 x Needle-Nose Combination Pliers (145 mm) 1000 V
11 06 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm²) 1000 V
87 26 250	1 x KNIPEX Cobra® VDE High-Tech Water Pump Pliers, insulated (2" / 46 mm) 1000 V
95 16 200	1 x Cable Shears with twin cutting edge (Ø 20 mm / 70 mm²) 1000 V
98 00 10	1 x Open-end wrench (10 mm) 1000 V
98 00 13	1 x Open-end wrench (13 mm) 1000 V

Content	
98 00 14	1 x Open-end wrench (14 mm) 1000 V
98 00 17	1 x Open-end wrench (17 mm) 1000 V
98 00 19	1 x Open-end wrench (19 mm) 1000 V
98 00 22	1 x Open-end wrench (22 mm) 1000 V
98 01 10	1 x Box Wrench (10 mm) 1000 V
98 01 13	1 x Box Wrench (13 mm) 1000 V
98 01 14	1 x Box Wrench (14 mm) 1000 V
98 01 17	1 x Box Wrench (17 mm) 1000 V
98 01 19	1 x Box Wrench (19 mm) 1000 V
98 01 22	1 x Box Wrench (22 mm) 1000 V
98 20 25	1 x Screwdrivers for slotted screws (0,4 x 2,5 x 75 mm) 1000 V
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (0,8 x 4 x 100 mm) 1000 V
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (1,0 x 5,5 x 125 mm) 1000 V
98 20 65 SL	1 x Screwdriver (Slim) for slotted screws (1,2 x 6,5 x 150 mm) 1000 V
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1 x 80 mm) 1000 V
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2 x 100 mm) 1000 V
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ1 x 80 mm) 1000 V
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ2 x 100 mm) 1000 V
98 40	1 x T-Handle Drive with driving square 1/2" (165 mm) 1000 V
98 42	1 x Reversible Ratchet with driving square 1/2" (5 - 50 NM in 0,25 Nm-Schritten) 1000 V
98 45 125	1 x Extension Bar with internal/external square 1/2" (+ 125 mm) 1000 V
98 45 250	1 x Extension Bar with internal/external square 1/2" (+ 250 mm) 1000 V
98 47 10	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (10 mm)

Content

	1000 V
98 47 11	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (11 mm) 1000 V
98 47 12	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (12 mm) 1000 V
98 47 13	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (13 mm) 1000 V
98 47 14	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (14 mm) 1000 V
98 47 17	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (17 mm) 1000 V
98 47 19	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (19 mm) 1000 V
98 47 22	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (22 mm) 1000 V
98 47 24	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (24 mm) 1000 V
98 52	1 x Cable Knife (190 mm) 1000 V
98 53 03	1 x Stripping Knife (155 mm) 1000 V
98 64 02	6 x Insulating clamps plastic 1000 V
70 06 160	1 x Knipex Diagonal Cutter (160 mm) 1000 V
98 25 02 SLS	1 x Knipex Screwdriver (Slim) Plus/Minus Pozidriv® (PZ/S2 x 100 mm) 1000 V

Accessories

98 99 15 LE	Tool Case "BIG Twin Move RED" empty,

technical change and errors excepted