

Product Datasheet model uvex pheos cx2 sonic 9309 275

**UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

**Product
characteristics**

- uvex's lightest compact wide-vision goggles (34 grams)
- high mechanical strength B (120 m/s)
- designation 3 (liquids), 4 (coarse dust) and T (extreme temperatures)
- comfortable protection thanks to soft forehead and nose piece moulded directly onto the lens
- uvex supravision coating technology
- very soft, light textile headband for secure and comfortable fit
- can be easily combined with other PPE

Technical details

Frame

Material
Colour

Front piece

PP/TPE
white, black

Material
Features
Colour

Headband

synthetic headband
individually adjustable
black, grey

Manufacturer's ID
code
Applicable EN norm
Field of use

Marking

W

166
3 (drops and splashes of liquid)
4 (large dust particles)

Impact resistance
Resistance to high
speed particles at
extremes of temp.
Conformity symbol

B (120 m/s)
T

CE

Lens

Material
Thickness
Coating
Colour
UV protection

PC
2,2 mm
uvex supravision extreme
clear
UV 400

Filter	Marking
Manufacturer's ID code	2C-1,2 (DIN EN 170)
Optical class	W
Impact resistance	1
Resistance to high speed particles at extremes of temp.	B (120 m/s)
Surface resistance to fine particles	T
Antifog	K
Conformity symbol	N
Factory symbol	CE
	
Miscellaneous	
Weight	34 g
Packing	5 spectacles per box 160 spectacles per cardboard box
Standards	DIN EN 166 + DIN EN 170
PPE Category	Category II