

**Kemo Electronic GmbH**

Mato Vukovic  
 Leher Landstr. 20  
 27607 Geestland  
 Germany

Phone: +49 4743 9338-0  
 Fax: +49 4743 9338-22

<http://www.kemo-electronic.de>  
 email: [info@kemo-electronic.de](mailto:info@kemo-electronic.de)

HR.Nr. HRB 111 486  
 UstNr: DE 814 380 369

**M240 - Power Control 230 V/AC, 10 A, Multifunction****\*\*\* NEW \*\*\***

Power controller for 230 V/AC consumers such as motors, lamps, many dimmable LEDs etc. The controller is overload- proof and can be controlled via a potentiometer (100 K lin.), a control voltage (0 - 10 V) or with PWM signals (0 - 100%, 100 - 10,000 Hz).

**Technical Data:**

Operating voltage: 220 - 230 V/AC 50 - 60 Hz

Max. connectable load: 10 Ampere (2,300 W)

Control mode: phase angle control

Switching-on: soft start

Operating display, overload display: 2-coloured LED

Control options: with potentiometer 100 K lin or control voltage 0 - 10 V/DC or PWM signal 3 - 24 V 100 - 10,000 Hz

The control signal input is completely isolated from the load control circuit.

Connections: Plug contacts flat plugs 6.3 mm and 2.8 mm

Dimensions: approx. 87 x 60 x 33 mm