

VE 100/12R

Wheel, with standard solid rubber tyre, with pressed steel rim

EAN 4047526275785

ID 275784

Customs tariff number 87169090



Tyre:

- standard solid rubber, hardness 80 Shore A
- very good operational comfort
- very good floor preservation, low-noise operation
- colour black

Rim:

- pressed steel
- zinc-plated, blue-passivated, Cr6-free

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, reduced load capacity over +60 °C



Technical data:

Wheel Ø (D)	☞	100 mm
Wheel width	⏏	30 mm
Load capacity at 4 km/h	⚖	70 kg
Load capacity (static)	⚖	175 kg
Bearing type	⦿	roller bearing
Axle bore Ø (d)		12 mm
Hub keyway (T1)	⌘	45 mm
Temperature resistance min		-25 °C
Temperature resistance max		80 °C
Tread and tyre hardness		80 Shore A
Unit weight	⚖	0.4 kg
Non-marking	✗	
Non-staining	✗	
Antistatic	⚡	✗
ProductDetail.TechnicalData.Esd	✗	
Electrically conductive	⚡	✗
Corrosion-resistant	✗	
Heat-resistant	🔥	✗
Tread hydrolysis-resistant	✗	
Suitable for autoclaves	✗	

Tread and tyre hardness

■ ■ ■ □ □ 80 Shore A

Rolling resistance

■ ■ □ □ □ satisfactory

Wear resistance

■ □ □ □ □ sufficient

Operating noise / floor surface preservation

■ ■ ■ ■ □ very good

