



HEADLED

HIGH POWER
LED HEADLAMP

- **LED Bulb:** 1pcs 3W LED+COB LED
- **Output:** 200 Lumen (3W LED), 180 lumen (COB LED)
- **Light power (1 Meter):**1050 lux (3W LED), 50 lux (COB LED)
- **Light range (1 Meter):** 65 meter (3W LED), 15 meter (COB LED)
- **Material:** ABS +PC body.
- **Special switch structure** – easy operating when wearing gloves
- **Rotate Switch Function:** Off - 3W LED - white COB LED
- **Product size (L x W x T):** 76 x 49 x 49 mm, 91g
- **Powered by 3XAAA batteries, NOT INCLUDED**
- **Alkaline battery running time:** 5.5 (3W High)
- Two sides of the head strap, One side with anti-slip epoxy for helmet
- Lamp can be slid off and strong magnet in the reverse
- 180° Rotation Structure to Protect Optical System



Designed and imported by HT Italia Srl



pak_HEADLEDBIlistArtw_1-01

Metel HA000766



8 033772 797054