



LC-M32-QHD-144-C - 31,5" curved monitor -

Experience the ultimate gaming feeling with the **31,5" / 80,01 cm** monitor from LC-Power!

Due to the **QHD** resolution of 2560 x 1440 pixels the monitor delivers 1,7 times razor-sharper pictures than conventional Full HD.

Immerse yourself in a fascinating gaming & entertainment world with a **1800R** curvature and a **16:9 widescreen format**.

Advanced **VA panel technology** minimizes light scatter across the entire screen and gives you deep blacks thanks to a contrast ratio of **3000:1**.

Other features of the monitor include a screen refresh rate of **144 Hz** for a very fluent display of content, **FreeSync** for a smooth gameplay as well as **FPS/RTS technology** for FPS and RTS games.

See sharper thanks to LC-Power!



Technical specification - LC-M32-QHD-144-C

Display size:	31,5" / 80,01 cm
Resolution:	QHD / 2560 x 1440 pixels
Screen refresh rate:	144 Hz
Panel type:	VA (Samsung)
Aspect ratio:	16:9
Brightness:	300 (± 20) cd/m ²
Contrast ratio:	3000:1
Display colours:	16,7 millions
Viewing angle:	H: 178° / V: 178°
Curvature:	1800R
Response time:	OD 4 ms
Interface:	1x HDMI / 1x DP / 1x DVI
Audio:	1x Audio out (3,5 mm jack)
Included in delivery:	monitor, base, DP cable, power cord, mounting material, user manual

Features:	FreeSync, Overdrive, Low Blue, GamePlus, FPS/RTS, Flicker-Free, VESA compatible
Colours:	back side: black base: black
Dimension (without base):	718 x 424 x 90 mm
Dimension (with base):	718 x 497 x 248 mm
Dimension (retail):	799 x 164 x 530 mm
Base tilt:	-5°~15°
VESA mounting:	75 x 75 mm
Weight (product/overall):	7,63 / 9,48 kg
Consumption:	42 W (typ.), 65 W (max.)
Standby:	≤ 0,5 W
Power input:	AC 100-240V 50/60Hz 1,5A
Energy labelling:	B
Mark of conformity:	CE
Barcode:	4260070127311
Manufacturer code:	LC-M32-QHD-144-C