



570E

Product no.: 570E

Tip cutter - straight long relieved head, for cutting at extreme tips




This head is suitable for horizontal and vertical cuts.



The long tips facilitate cutting in hard-to-reach areas.



For cutting at extreme tips



[source images](#)

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 500 Micro is a full range of medium sized, robust, precision cutters with a wide range of head shapes. The cutters are manufactured from high grade tool steel. The cutting edges are hardened to Rockwell 63-65 HRC. The precision cutters have a nonreflecting surface, are ESD safe and resharable.

		Type	Type of Cut	Cutting Capacity
		Series 500 Medium		
		mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0		
		Inch .0001 .0003 .0007 .0011 .0015 .0019 .0023 .0027 .0031 .0035 .0039 .0043 .0047 .0051 .0055 .0059 .0062 .0066 .0070 .0074 .0078		
	512N		Semi Flush	
	512E		Semi Flush	
	599T		Semi Flush / Carbide	
	522N		Flush	
	599E		Flush	
	532N		Super Full Flush	
	576TX1		Flush / Carbide	
	503E		Flush	
	503ETST 30°		Flush / Carbide	
	504AE		Flush	
	555E 35°		Flush	
	572E 40°		Flush	
	582E 45°		Flush	
	593AE 30°		Flush	
	575E 45°		Flush	
	592E		Flush	
	792E		Super Full Flush	
	576TX		Flush / Carbide	
	570E		Flush	
	573E		Flush	
				for vertical tip cutting





Technical Data

Length mm	120
Length of cutting edges mm	5
Head width mm	11
Head thickness mm	6
Head length mm	29.5
Max. cutting capability – hard wire mm	---
Weight in oz	2.427
Length of cutting edges Inches	0.197
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.161
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,4
Max. cutting capability – copper wire mm	Ø 0,6
Length inches	4.724
Weight in g	68.8
Erem applications	Microelectronic