

RT Pico



WX

RT Micro



WX



WT

RT Ultra



WX




Soldering Iron: WXPP ○ / WXPP MS ●

Soldering Iron: WXMP ○ / WXMP MS ● / WMRP ○ / WMRP MS ●

Soldering Iron: WXUP MS ●


| | article | a / b (mm) (inch) | | article | a / b (mm) (inch) | | article | a / b (mm) (inch) |
|----------------------|---|---------------------------|---|---|----------------------------|---|--------------------------------------|---------------------------|
| Conical | RTP 001 C T0050103199 RTP 001 C MS T0050107399 | 0.1 / 0.004 | ● | RTM 001 C NW T005446299N RTM 001 C NW MS T0054462571N | 0.1 / 0.004 | ● | RTU 004 C MS T0050104999 | 0.4 / 0.016 |
| | RTP 001 C NW T0050103299 RTP 001 C MS NW T0050101499 | 0.1 / 0.004 | ● | RTM 002 C T0054460199N RTM 002 C MS T0054461499N | 0.2 / 0.008 | ● | RTU 008 C MS T0050105099 | 0.8 / 0.031 |
| | RTP 002 C T0050103999 RTP 002 C MS T0050101599 | 0.2 / 0.008 | ● | RTM 002 C L T0050100099 RTM 002 C L MS T0050100199 | 0.2 / 0.008 | ● | RTU 016 C MS T0050105199 | 1.6 / 0.063 |
| | RTP 004 C T0050103999 RTP 004 C MS T0050101699 | 0.4 / 0.016 | ● | RTM 004 C X MS T005446399N | 0.4 / 0.016 | ● | RTU 004 C X MS T0050105299 | 0.4 / 0.016 |
| | RTP 001 C X T0050103999 RTP 001 C X MS T0050101799 | 0.1 / 0.004 | ● | RTM 005 C X MS T0054463299N | 0.5 / 0.019 | ● | RTU 008 C X MS T0050105399 | 0.8 / 0.031 |
| | RTP 002 C X T0050103999 RTP 002 C X MS T0050101899 | 0.2 / 0.008 | ● | RTM 008 C T0054460299N RTM 008 C MS T0054461799N | 0.8 / 0.031 | ● | RTU 016 C X MS T0050105499 | 1.6 / 0.063 |
| Bevel Cut | RTP 004 B T0050103799 RTP 004 B MS T0050101999 | 0.4 / 0.016 | ● | RTM 004 B T0050100299 RTM 004 B MS T0050100399 | 0.4 / 0.016 | ● | RTU 020 B MS T0050105599 | 2.0 / 0.079 |
| | RTP 012 B T0050103899 RTP 012 B MS T0050102099 | 1.2 / 0.047 | ● | RTM 012 B T0054460699N RTM 012 B MS | 1.2 / 0.047 | ● | RTU 035 B MS T0050105699 | 3.5 / 0.138 |
| | | | | | | | RTU 050 B MS T0050105799 | 5.0 / 0.197 |
| Chisel | RTP 002 S T0050103999 RTP 002 S MS T0050102199 | 0.2 / 0.1 / 0.008 / 0.004 | ● | RTM 003 S NW T0054462699N RTM 003 S NW MS T0054462671N | 0.3 / 0.1 / 0.012 / 0.004 | ● | RTU 015 S MS T0050105899 | 1.5 / 0.4 / 0.059 / 0.016 |
| | RTP 002 S NW T0050104099 RTP 002 S NW MS T0050102299 | 0.2 / 0.1 / 0.008 / 0.004 | ● | RTM 004 S T0054461299N RTM 004 S MS T0054461599N | 0.4 / 0.15 / 0.016 / 0.006 | ● | RTU 022 S MS T0050105999 | 2.2 / 0.6 / 0.087 / 0.024 |
| | RTP 004 S T0050104199 RTP 004 S MS T0050102399 | 0.4 / 0.2 / 0.016 / 0.008 | ● | RTM 006 S MS T0050100499 | 0.6 / 0.4 / 0.024 / 0.016 | ● | RTU 032 S MS T0050106099 | 3.2 / 0.8 / 0.126 / 0.031 |
| | RTP 008 S T0050104299 RTP 008 S MS T0050102499 | 0.8 / 0.3 / 0.031 / 0.012 | ● | RTM 008 S T0054460999N RTM 008 S MS T0054462399N | 0.8 / 0.4 / 0.031 / 0.016 | ● | RTU 032 S L MS T0050106199 | 3.2 / 0.8 / 0.126 / 0.031 |
| | RTP 010 S T0050104399 RTP 010 S MS T0050102599 | 1.0 / 0.3 / 0.039 / 0.012 | ● | RTM 008 S X T0054460599N RTM 008 S X MS T0054461999N | 0.8 / 0.4 / 0.031 / 0.016 | ● | RTU 050 S MS T0050106299 | 5.0 / 1.2 / 0.197 / 0.047 |
| | RTP 013 S T0050104499 RTP 013 S MS T0050102699 | 1.3 / 0.3 / 0.051 / 0.012 | ● | RTM 010 S T0050100599 RTM 010 S MS T0050100699 | 1.0 / 0.3 / 0.039 / 0.012 | ● | RTU 076 S MS T0050106399 | 7.6 / 1.5 / 0.299 / 0.059 |
| | | | | RTM 013 S T0054460399N RTM 013 S MS T0054461699N | 1.3 / 0.4 / 0.051 / 0.016 | ● | RTU 093 S MS T0050106499 | 9.3 / 2.0 / 0.366 / 0.079 |
| | | | | RTM 013 S X MS T0054460373N | 1.3 / 0.5 / 0.051 / 0.019 | ● | | |
| | | | | RTM 015 S T0054460499N RTM 015 S MS T0054461899N | 1.5 / 0.4 / 0.059 / 0.016 | ● | | |
| | | | | RTM 018 S T0050100799 RTM 018 S MS T0050100899 | 1.8 / 0.4 / 0.071 / 0.016 | ● | | |
| | | | RTM 022 S T0054460899N RTM 022 S MS T0054462299N | 2.2 / 0.4 / 0.087 / 0.016 | ● | | | |
| | | | RTM 032 S T0050100999 RTM 032 S MS T0050101099 | 3.2 / 0.9 / 0.126 / 0.035 | ● | | | |
| | | | RTM 036 S T0054461999N RTM 036 S MS T0054463199N | 3.6 / 0.9 / 0.141 / 0.035 | ● | | | |
| Knife | RTP 010 K T0050104599 RTP 010 K MS T0050102799 | 1.0 / 0.039 | ● | RTM 025 K T0050101199 RTM 025 K MS T0050101299 | 2.5 / 0.098 | ● | | |
| | RTP 010 K NW T0050104699 RTP 010 K MS NW T0050102899 | 1.0 / 0.039 | ● | RTM 030 K T0054460799N RTM 030 K MS T0054462199N | 3.0 / 0.118 | ● | | |
| | RTP 025 K T0050104799 RTP 025 K MS T0050102999 | 2.5 / 0.098 | ● | | | | | |
| Gullwing | RTP 020 G T0050104899 RTP 020 G MS T0050103099 | 2.0 / 0.079 | ● | RTM 020 G T0054461999N RTM 020 G MS T0054462499N | 2.0 / 0.079 | ● | RTU 020 G MS T0050106599 | 2.0 / 0.079 |
| | | | | | | | | |

NO COMPROMISE.
PRECISION. PERFORMANCE. POWER.
 EXPLORE THE NEW ACTIVE SOLDERING TIP RANGE




- Standard tip
- Mil-Spec soldering tip
- not wettable

Measuring tip



Blade



Weller®

www.weller-tools.com/nocompromise