

RT Pico



WX

RT Micro



WX



WT

RT Ultra



WX




Soldering Iron: WXPP ○ / WXPP MS ●

Soldering Iron: WXMP ○ / WXMP MS ● / WMRP ○ / WMRP MS ●

Soldering Iron: WXUP MS ●


	article	a / b (mm) (inch)		article	a / b (mm) (inch)		article	a / b (mm) (inch)
Conical 	RTP 001 C T0050103199 RTP 001 C MS T0050107399	0.1 / 0.004	●	RTM 001 C NW T005446299N RTM 001 C NW MS T0054462571N	0.1 / 0.004	●	RTU 004 C MS T0050104999	0.4 / 0.016
	RTP 001 C NW T0050103299 RTP 001 C MS NW T0050101499	0.1 / 0.004	●	RTM 002 C T0054460199N RTM 002 C MS T0054461499N	0.2 / 0.008	●	RTU 008 C MS T0050105099	0.8 / 0.031
	RTP 002 C T0050103999 RTP 002 C MS T0050101599	0.2 / 0.008	●	RTM 002 C L T0050100099 RTM 002 C L MS T0050100199	0.2 / 0.008	●	RTU 016 C MS T0050105199	1.6 / 0.063
	RTP 004 C T0050103999 RTP 004 C MS T0050101699	0.4 / 0.016	●	RTM 004 C X MS T005446399N	0.4 / 0.016	●	RTU 004 C X MS T0050105299	0.4 / 0.016
	RTP 001 C X T0050103999 RTP 001 C X MS T0050101799	0.1 / 0.004	●	RTM 005 C X MS T0054463299N	0.5 / 0.019	●	RTU 008 C X MS T0050105399	0.8 / 0.031
	RTP 002 C X T0050103999 RTP 002 C X MS T0050101899	0.2 / 0.008	●	RTM 008 C T0054460299N RTM 008 C MS T0054461799N	0.8 / 0.031	●	RTU 016 C X MS T0050105499	1.6 / 0.063
Bevel Cut 	RTP 004 B T0050103799 RTP 004 B MS T0050101999	0.4 / 0.016	●	RTM 004 B T0050100299 RTM 004 B MS T0050100399	0.4 / 0.016	●	RTU 020 B MS T0050105599	2.0 / 0.079
	RTP 012 B T0050103899 RTP 012 B MS T0050102099	1.2 / 0.047	●	RTM 012 B T0054460699N RTM 012 B MS	1.2 / 0.047	●	RTU 035 B MS T0050105699	3.5 / 0.138
							RTU 050 B MS T0050105799	5.0 / 0.197
Chisel 	RTP 002 S T0050103999 RTP 002 S MS T0050102199	0.2 / 0.1 / 0.008 / 0.004	●	RTM 003 S NW T0054462699N RTM 003 S NW MS T0054462671N	0.3 / 0.1 / 0.012 / 0.004	●	RTU 015 S MS T0050105899	1.5 / 0.4 / 0.059 / 0.016
	RTP 002 S NW T0050104099 RTP 002 S NW MS T0050102299	0.2 / 0.1 / 0.008 / 0.004	●	RTM 004 S T0054461299N RTM 004 S MS T0054461599N	0.4 / 0.15 / 0.016 / 0.006	●	RTU 022 S MS T0050105999	2.2 / 0.6 / 0.087 / 0.024
	RTP 004 S T0050104199 RTP 004 S MS T0050102399	0.4 / 0.2 / 0.016 / 0.008	●	RTM 006 S MS T0050100499	0.6 / 0.4 / 0.024 / 0.016	●	RTU 032 S MS T0050106099	3.2 / 0.8 / 0.126 / 0.031
	RTP 008 S T0050104299 RTP 008 S MS T0050102499	0.8 / 0.3 / 0.031 / 0.012	●	RTM 008 S T0054460999N RTM 008 S MS T0054462399N	0.8 / 0.4 / 0.031 / 0.016	●	RTU 032 S L MS T0050106199	3.2 / 0.8 / 0.126 / 0.031
	RTP 010 S T0050104399 RTP 010 S MS T0050102599	1.0 / 0.3 / 0.039 / 0.012	●	RTM 008 S X T0054460599N RTM 008 S X MS T0054461999N	0.8 / 0.4 / 0.031 / 0.016	●	RTU 050 S MS T0050106299	5.0 / 1.2 / 0.197 / 0.047
	RTP 013 S T0050104499 RTP 013 S MS T0050102699	1.3 / 0.3 / 0.051 / 0.012	●	RTM 010 S T0050100599 RTM 010 S MS T0050100699	1.0 / 0.3 / 0.039 / 0.012	●	RTU 076 S MS T0050106399	7.6 / 1.5 / 0.299 / 0.059
				RTM 013 S T0054460399N RTM 013 S MS T0054461699N	1.3 / 0.4 / 0.051 / 0.016	●	RTU 093 S MS T0050106499	9.3 / 2.0 / 0.366 / 0.079
				RTM 013 S X MS T0054460373N	1.3 / 0.5 / 0.051 / 0.019	●		
				RTM 015 S T0054460499N RTM 015 S MS T0054461899N	1.5 / 0.4 / 0.059 / 0.016	●		
				RTM 018 S T0050100799 RTM 018 S MS T0050100899	1.8 / 0.4 / 0.071 / 0.016	●		
			RTM 022 S T0054460899N RTM 022 S MS T0054462299N	2.2 / 0.4 / 0.087 / 0.016	●			
			RTM 032 S T0050100999 RTM 032 S MS T0050101099	3.2 / 0.9 / 0.126 / 0.035	●			
			RTM 036 S T0054461999N RTM 036 S MS T0054463199N	3.6 / 0.9 / 0.141 / 0.035	●			
Knife 	RTP 010 K T0050104599 RTP 010 K MS T0050102799	1.0 / 0.039	●	RTM 025 K T0050101199 RTM 025 K MS T0050101299	2.5 / 0.098	●		
	RTP 010 K NW T0050104699 RTP 010 K MS NW T0050102899	1.0 / 0.039	●	RTM 030 K T0054460799N RTM 030 K MS T0054462199N	3.0 / 0.118	●		
	RTP 025 K T0050104799 RTP 025 K MS T0050102999	2.5 / 0.098	●					
Gullwing 	RTP 020 G T0050104899 RTP 020 G MS T0050103099	2.0 / 0.079	●	RTM 020 G T0054461999N RTM 020 G MS T0054462499N	2.0 / 0.079	●	RTU 020 G MS T0050106599	2.0 / 0.079

NO COMPROMISE.
PRECISION. PERFORMANCE. POWER.
 EXPLORE THE NEW ACTIVE SOLDERING TIP RANGE



- Standard tip
- Mil-Spec soldering tip
- not wettable

Measuring tip



Blade

RTU 100 K MS T0050106699	10.0 / 0.393
RTU 160 K MS T0050106799	16.0 / 0.630
RTU 200 K MS T0050106899	20.0 / 0.078
RTU 330 K MS T0050106999	33.0 / 1.299

Weller®

www.weller-tools.com/nocompromise