

# RT Pico



WX

# RT Micro



WX



WT

# RT Ultra




WX




	Soldering Iron: WXPP ○ / WXPP MS ●			Soldering Iron: WXMP ○ / WXMP MS ● / WMRP ○ / WMRP MS ●			Soldering Iron: WXUP MS ●		
	article	a / b (mm) (inch)		article	a / b (mm) (inch)		article	a / b (mm) (inch)	
<b>Conical</b> 	<b>RTP 001 C</b> T0050103199 <b>RTP 001 C MS</b> T0050107399	0.1 / 0.004		<b>RTM 001 C NW</b> T005446299N <b>RTM 001 C NW MS</b> T0054462571N	0.1 / 0.004	●	<b>RTU 004 C MS</b> T0050104999	0.4 / 0.016	
	<b>RTP 001 C NW</b> T0050103299 <b>RTP 001 C MS NW</b> T0050101499	0.1 / 0.004	●	<b>RTM 002 C</b> T0054460199N <b>RTM 002 C MS</b> T0054461499N	0.2 / 0.008		<b>RTU 008 C MS</b> T0050105099	0.8 / 0.031	
	<b>RTP 002 C</b> T0050103399 <b>RTP 002 C MS</b> T0050101599	0.2 / 0.008		<b>RTM 002 C L</b> T0050100099 <b>RTM 002 C L MS</b> T0050100199	0.2 / 0.008		<b>RTU 016 C MS</b> T0050105199	1.6 / 0.063	
	<b>RTP 004 C</b> T0050103499 <b>RTP 004 C MS</b> T0050101699	0.4 / 0.016		<b>RTM 004 C X MS</b> T0054463399N	0.4 / 0.016		<b>RTU 004 C X MS</b> T0050105299	0.4 / 0.016	
	<b>RTP 001 C X</b> T0050103599 <b>RTP 001 C X MS</b> T0050101799	0.1 / 0.004		<b>RTM 005 C X MS</b> T0054463299N	0.5 / 0.019		<b>RTU 008 C X MS</b> T0050105399	0.8 / 0.031	
	<b>RTP 002 C X</b> T0050103699 <b>RTP 002 C X MS</b> T0050101899	0.2 / 0.008		<b>RTM 008 C</b> T0054460299N <b>RTM 008 C MS</b> T0054461799N	0.8 / 0.031		<b>RTU 016 C X MS</b> T0050105499	1.6 / 0.063	
<b>Bevel Cut</b> 	<b>RTP 004 B</b> T0050103799 <b>RTP 004 B MS</b> T0050101999	0.4 / 0.016		<b>RTM 004 B</b> T0050100299 <b>RTM 004 B MS</b> T0050100399	0.4 / 0.016		<b>RTU 020 B MS</b> T0050105599	2.0 / 0.079	
	<b>RTP 012 B</b> T0050103899 <b>RTP 012 B MS</b> T0050102099	1.2 / 0.047		<b>RTM 012 B</b> T0054460699N <b>RTM 012 B MS</b> T0054461799N	1.2 / 0.047	45°	<b>RTU 035 B MS</b> T0050105699	3.5 / 0.138	
							<b>RTU 050 B MS</b> T0050105799	5.0 / 0.197	
<b>Chisel</b> 	<b>RTP 002 S</b> T0050103999 <b>RTP 002 S MS</b> T0050102199	0.2 / 0.1 / 0.008 / 0.004		<b>RTM 003 S NW</b> T0054462699N <b>RTM 003 S NW MS</b> T0054462671N	0.3 / 0.1 / 0.012 / 0.004	●	<b>RTU 015 S MS</b> T0050105899	1.5 / 0.4 / 0.059 / 0.016	
	<b>RTP 002 S NW</b> T0050104099 <b>RTP 002 S NW MS</b> T0050102299	0.2 / 0.1 / 0.008 / 0.004	●	<b>RTM 004 S</b> T0054461299N <b>RTM 004 S MS</b> T0054461599N	0.4 / 0.15 / 0.016 / 0.006		<b>RTU 022 S MS</b> T0050105999	2.2 / 0.6 / 0.087 / 0.024	
	<b>RTP 004 S</b> T0050104199 <b>RTP 004 S MS</b> T0050102399	0.4 / 0.2 / 0.016 / 0.008		<b>RTM 006 S MS</b> T0050100499	0.6 / 0.4 / 0.024 / 0.016		<b>RTU 032 S MS</b> T0050106099	3.2 / 0.8 / 0.126 / 0.031	
	<b>RTP 008 S</b> T0050104299 <b>RTP 008 S MS</b> T0050102499	0.8 / 0.3 / 0.031 / 0.012		<b>RTM 008 S</b> T0054460999N <b>RTM 008 S MS</b> T0054462399N	0.8 / 0.4 / 0.031 / 0.016		<b>RTU 032 S L MS</b> T0050106199	3.2 / 0.8 / 0.126 / 0.031	
	<b>RTP 010 S</b> T0050104399 <b>RTP 010 S MS</b> T0050102599	1.0 / 0.3 / 0.039 / 0.012		<b>RTM 008 S X</b> T0054460599N <b>RTM 008 S X MS</b> T0054461999N	0.8 / 0.4 / 0.031 / 0.016		<b>RTU 050 S MS</b> T0050106299	5.0 / 1.2 / 0.197 / 0.047	
	<b>RTP 013 S</b> T0050104499 <b>RTP 013 S MS</b> T0050102699	1.3 / 0.3 / 0.051 / 0.012		<b>RTM 010 S</b> T0050100599 <b>RTM 010 S MS</b> T0050100699	1.0 / 0.3 / 0.039 / 0.012		<b>RTU 076 S MS</b> T0050106399	7.6 / 1.5 / 0.299 / 0.059	
				<b>RTM 013 S</b> T0054460399N <b>RTM 013 S MS</b> T0054461699N	1.3 / 0.4 / 0.051 / 0.016		<b>RTU 093 S MS</b> T0050106499	9.3 / 2.0 / 0.366 / 0.079	
				<b>RTM 013 S X MS</b> T0054460373N	1.3 / 0.5 / 0.051 / 0.019				
				<b>RTM 015 S</b> T0054460499N <b>RTM 015 S MS</b> T0054461899N	1.5 / 0.4 / 0.059 / 0.016				
				<b>RTM 018 S</b> T0050100799 <b>RTM 018 S MS</b> T0050100899	1.8 / 0.4 / 0.071 / 0.016				
			<b>RTM 022 S</b> T0054460899N <b>RTM 022 S MS</b> T0054462299N	2.2 / 0.4 / 0.087 / 0.016					
			<b>RTM 032 S</b> T0050100999 <b>RTM 032 S MS</b> T0050101099	3.2 / 0.9 / 0.126 / 0.035					
			<b>RTM 036 S</b> T0054461999N <b>RTM 036 S MS</b> T0054463199N	3.6 / 0.9 / 0.141 / 0.035					
<b>Knife</b> 	<b>RTP 010 K</b> T0050104599 <b>RTP 010 K MS</b> T0050102799	1.0 / 0.039		<b>RTM 025 K</b> T0050101199 <b>RTM 025 K MS</b> T0050101299	2.5 / 0.098				
	<b>RTP 010 K NW</b> T0050104699 <b>RTP 010 K MS NW</b> T0050102899	1.0 / 0.039	●	<b>RTM 030 K</b> T0054460799N <b>RTM 030 K MS</b> T0054462199N	3.0 / 0.118	45°			
	<b>RTP 025 K</b> T0050104799 <b>RTP 025 K MS</b> T0050102999	2.5 / 0.098							
<b>Gullwing</b> 	<b>RTP 020 G</b> T0050104899 <b>RTP 020 G MS</b> T0050103099	2.0 / 0.079		<b>RTM 020 G</b> T0054461999N <b>RTM 020 G MS</b> T0054462499N	2.0 / 0.079		<b>RTU 020 G MS</b> T0050106599	2.0 / 0.079	

**NO COMPROMISE.**  
**PRECISION. PERFORMANCE. POWER.**  
 EXPLORE THE NEW ACTIVE SOLDERING TIP RANGE



- Standard tip
- Mil-Spec soldering tip
- not wettable

### Measuring tip



### Blade

<b>RTU 100 K MS</b> T0050106699	10.0 / 0.393
<b>RTU 160 K MS</b> T0050106799	16.0 / 0.630
<b>RTU 200 K MS</b> T0050106899	20.0 / 0.078
<b>RTU 330 K MS</b> T0050106999	33.0 / 1.299

# Weller®

www.weller-tools.com/nocompromise