

RT Pico



WX

RT Micro



WX



WT

RT Ultra



WX



Soldering Iron: WXPP ○ / WXPP MS ●

Soldering Iron: WXMP ○ / WXMP MS ● / WMRP ○ / WMRP MS ●

Soldering Iron: WXUP MS ●

	article	a / b (mm) (inch)		article	a / b (mm) (inch)		article	a / b (mm) (inch)
Conical 	RTP 001 C T0050103199	0.1	○	RTM 001 C NW T0054462599N	0.1	○	RTU 004 C MS T0050104999	0.4
	RTP 001 C MS T0050107399	0.004	●	RTM 001 C NW MS T0054462571N	0.004	●	RTU 008 C MS T0050105099	0.8
	RTP 001 C NW T0050103299	0.1	○	RTM 002 C T0054460199N	0.2	○	RTU 016 C MS T0050105199	1.6
	RTP 001 C MS NW T0050101499	0.004	●	RTM 002 C MS T0054461499N	0.008	●	RTU 004 C X MS T0050105299	0.4
	RTP 002 C T0050103399	0.2	○	RTM 002 C L T0050100099	0.2	○	RTU 008 C X MS T0050105399	0.8
	RTP 002 C MS T0050101599	0.008	●	RTM 002 C L MS T0050100199	0.008	●	RTU 016 C X MS T0050105499	1.6
	RTP 004 C T0050103499	0.4	○	RTM 004 C X MS T0054463399N	0.4	○		
	RTP 004 C MS T0050101699	0.016	●	RTM 005 C X MS T0054463299N	0.5	○		
RTP 001 C X T0050103599	0.1	○	RTM 008 C T0054460299N	0.8	○			
RTP 001 C X MS T0050101799	0.004	●	RTM 008 C MS T0054461799N	0.031	●			
RTP 002 C X T0050103699	0.2	○						
RTP 002 C X MS T0050101899	0.008	●						

Bevel Cut 	RTP 004 B T0050103799	0.4	○	RTM 004 B T0050100299	0.4	○	RTU 020 B MS T0050105599	2.0
	RTP 004 B MS T0050101999	0.016	●	RTM 004 B MS T0050100399	0.016	●	RTU 035 B MS T0050105699	3.5
	RTP 012 B T0050103899	1.2	○	RTM 012 B T0054460699N	1.2	○	RTU 050 B MS T0050105799	5.0
RTP 012 B MS T0050102099	0.047	●	RTM 012 B MS T0054460699N	0.047	●			

Chisel 	RTP 002 S T0050103999	0.2 / 0.1	○	RTM 003 S NW T0054462699N	0.3 / 0.1	○	RTU 015 S MS T0050105899	1.5 / 0.4
	RTP 002 S MS T0050102199	0.008 / 0.004	●	RTM 003 S NW MS T0054462671N	0.012 / 0.004	●	RTU 022 S MS T0050105999	2.2 / 0.6
	RTP 002 S NW T0050104099	0.2 / 0.1	○	RTM 004 S T0054461299N	0.4 / 0.15	○	RTU 032 S MS T0050106099	3.2 / 0.8
	RTP 002 S NW MS T0050102299	0.008 / 0.004	●	RTM 004 S MS T0054461599N	0.016 / 0.006	●	RTU 032 S L MS T0050106199	3.2 / 0.8
	RTP 004 S T0050104199	0.4 / 0.2	○	RTM 006 S MS T0050100499	0.6 / 0.4	○	RTU 050 S MS T0050106299	5.0 / 1.2
	RTP 004 S MS T0050102399	0.016 / 0.008	●	RTM 008 S T0054460999N	0.8 / 0.4	○	RTU 076 S MS T0050106399	7.6 / 1.5
	RTP 008 S T0050104299	0.8 / 0.3	○	RTM 008 S MS T0054462399N	0.031 / 0.016	●	RTU 093 S MS T0050106499	9.3 / 2.0
	RTP 008 S MS T0050102499	0.031 / 0.012	●	RTM 008 S X T0054460599N	0.8 / 0.4	○		
	RTP 010 S T0050104399	1.0 / 0.3	○	RTM 008 S X MS T0054461999N	0.031 / 0.016	●		
	RTP 010 S MS T0050102599	0.039 / 0.012	●	RTM 010 S T0050100599	1.0 / 0.3	○		
	RTP 013 S T0050104499	1.3 / 0.3	○	RTM 010 S MS T0050100699	0.039 / 0.012	●		
	RTP 013 S MS T0050102699	0.051 / 0.012	●	RTM 013 S T0054460399N	1.3 / 0.4	○		
				RTM 013 S MS T0054461699N	0.051 / 0.016	●		

				RTM 013 S X MS T0054460373N	1.3 / 0.5	○		
				RTM 015 S T0054460499N	1.5 / 0.4	○		
				RTM 015 S MS T0054461899N	0.059 / 0.016	●		
				RTM 018 S T0050100799	1.8 / 0.4	○		
				RTM 018 S MS T0050100899	0.071 / 0.016	●		
				RTM 022 S T0054460899N	2.2 / 0.4	○		
				RTM 022 S MS T0054462299N	0.087 / 0.016	●		
				RTM 032 S T0050100999	3.2 / 0.9	○		
				RTM 032 S MS T0050101099	0.126 / 0.035	●		
				RTM 036 S T0054461999N	3.6 / 0.9	○		
				RTM 036 S MS T0054463199N	0.141 / 0.035	●		

RT Pico 40 watts

RT Micro 40 watts

RT Ultra 150 watts

NO COMPROMISE.
PRECISION. PERFORMANCE. POWER.
 EXPLORE THE NEW ACTIVE SOLDERING TIP RANGE

Knife 	RTP 010 K T0050104599	1.0	○	RTM 025 K T0050101199	2.5	○		
	RTP 010 K MS T0050102799	0.039	●	RTM 025 K MS T0050101299	0.098	●		
	RTP 010 K NW T0050104699	1.0	○	RTM 030 K T0054460799N	3.0	○		
RTP 010 K MS NW T0050102899	0.039	●	RTM 030 K MS T0054462199N	0.118	●			
RTP 025 K T0050104799	2.5	○						
RTP 025 K MS T0050102999	0.098	●						
Gullwing 	RTP 020 G T0050104899	2.0	○	RTM 020 G T0054461999N	2.0	○	RTU 020 G MS T0050106599	2.0
	RTP 020 G MS T0050103099	0.079	●	RTM 020 G MS T0054462499N	0.079	●		

- Standard tip
- Mil-Spec soldering tip
- not wettable

Measuring tip 	RTM 028 X T0054461399N			Blade 	RTU 100 K MS T0050106699	10.0	
					RTU 160 K MS T0050106799	16.0	
					RTU 200 K MS T0050106899	20.0	
					RTU 330 K MS T0050106999	33.0	
						1.299	

Weller®

www.weller-tools.com/nocompromise