



Part No	90NB0MN2-M02190
Model Name	F705QA-BX140T
EAN Code	4718017462990
UPC Code	192876462997
LCD Cover Color & Decoration	Star Grey_IMR
Top Case Color & Decoration	Grey_IMR
On board processor	AMD Quad Core A12-9720P Processor, 2.7 GHz (2M Cache, up to 3.6 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	17.3'//Slim 200nits//HD+ 1600x900 16:9//Anti-Glare//NTSC: 60%
Number Pad	N/A
ScreenPad™	N/A
Chipset	N/A
Memory Slot	2x
Total System Memory	DRAM DDR4 8GB
On board memory	N/A
Memory Max.	16G
DIMM Memory	DRAM DDR4 8GB
Storage	PCIeG3x2 NVME 256GB M.2 SSD
Expansion Slot	DDR4*1 M.2 2280 SATA3 *1 STD 2.5" SATA HDD *1
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	AMD Radeon R7 graphics
Video memory	N/A
Video Camera	VGA Web Camera (Fixed type)
FingerPrint	N/A
On board Wireless	N/A
Wireless(Module)	Wi-Fi 5(802.11ac)+Bluetooth 4.1 (Dual band) 1*1
LAN	10/100/1000 Mbps
Card Reader	Spec: SDXC
USB Port	2x USB 2.0 1x USB3.1 Type A (Gen1) 1x USB3.1 Type C (Gen 1)

Interface	1x Headphone-out & Audio-in Combo Jack 1x RJ45 LAN Jack for LAN insert 1x HDMI 1x USB3.1-Type C(Gen1)
Audio	Sonic Master
Weight (Kg)	2.00 KG (Without Battery) 2.10 KG (with 3 cell battery)
Dimension (cm)	41.1(W) x 27.0(D) x 2.20 ~ 2.30 (H) cm
AC Adapter	ø5.5 45W AC Adapter Output: 19V DC, 2.37A, 45W , Input: 100~240V AC 50/60Hz universal
Battery	42WHrs, 3S1P, 3-cell Li-ion
Replaceable Battery	No
Keyboard type	Chiclet Keyboard
Software	ASUS Live Update ATK Package(ASUS On Screen Display) CyberLink PhotoDirector 5 CyberLink PowerDirector 12 Dr. Eye ASUS GiftBox ASUS Splendid Avast SecureLine ICESound McAfee Internet Security(Trial version)
Security	TPM (Firmware TPM) BIOS Booting User Password Protection
Supplied Accessories	

