

# **PRODUCT DATASHEET**LEDstixx

**LEDstixx | Little helpers** 



## **AREAS OF APPLICATION**

- Sideboards
- Flower arrangements
- Practical adhesive surface or drill holes
- Horizontal or vertical alignment on walls or objects

## **PRODUCT BENEFITS**

- Very compact LED luminaire

#### **PRODUCT FEATURES**

- Modern luminaire
- High-quality aluminum casing



# **TECHNICAL DATA**

## Electrical data

Nominal wattage	0.6 W
Operating mode	Battery
Nominal voltage	4.5 V


#### Photometrical data

Color temperature	6200 K
Color rendering index Ra	≥80
Luminous flux	25 lm
Luminous efficacy	42 lm/W

# Light technical data

Beam angle	90.00 °
beam angle	70.00

# Dimensions & weight



Length	222.0 mm
Width	16.2 mm
Height	22.0 mm
Product weight	94.00 g

## Colors & materials

Body material	Aluminum
Product color	Silver
Housing color	Silver

# Temperatures & operating conditions

	Ambient temperature range	-20+60 °C
--	---------------------------	-----------

## Lifespan

Number of switching cycles	100000
Lifespan	10000 h

# Additional product data

Mounting type	Surface
Mounting location	Wall

# Capabilities

Dimmable	No
LED module replaceable	Not replaceable

#### Certificates & standards

Protection class	Ш
Type of protection	IP20
Standards	CE

# **LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075227866	Role 1	72 mm x 72 mm x 280 mm	171.00 g	1.45 dm <sup>3</sup>
4058075227873	Shipping carton box 6	230 mm x 160 mm x 283 mm	1297.00 g	10.41 dm³
4058075227880	Shipping carton box 24	537 mm x 337 mm x 283 mm	6128.00 g	51.21 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## **DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.