



BN:2181305

DC power cable MN:DC-2J21-90-XL

- 1) Cable length: 2M
- 2) Plug style: straight angle
- 3) Pin: 9.5mm
- 4) Plated Tim: 6 mm (Length)
- 5) double cable: 2x0.4mm²
- 6) Out dia.: 5.5mm, inner dia. 2.1mm.
- 7) Color: Red/Black
- 8) max.operating voltage and current: 36V 5A
- 9)-Red cable: outer dia: 2.5mm and inner dia: 0.8mm- Black cable: outer dia: 2.5mm and inner dia: 0.8mm
- 10) black plastic housing: L25MM,H8.5MM,D16MM