

VOLTcraft® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

K TYPE PROBE, -50 TO 400 DEGREE C, VOLTcraft TYP K

CE
VERSION 12/21

N° 2181321

The thermocouple with heat-resistant and metal-sheathed connection cable is suitable for use in warm environments (cable only).

HIGHLIGHTS:

Wire thermocouple with heat-resistant and metal-sheathed connection cable // Cable length 1m // Measuring range temperature -50 to +400 °C

TECHNICAL DATA:

Cable length	1.0 m
Response time	> 5 s
Measuring range temperature	-50 to +400 °C
Connection	Thermocouple Connector
Sensor type	K TYPE
Accuracy temperature	± 2.5 °C
Product Type	Air Probe

PACKAGE CONTENTS:

K Type Probe

