




客户料号: 2182166
产品图号: MWC12033BK

版次: A/1
详细描述: 更新标签内容
变更日期: 2020.11.25
变更者: 梁静雅



技术要求: requirement:

- 1: 耐压测试: 外高压4200V/S; 内高压2500V/S; 0.5MA Dielectric voltage :between jacket and conductors 4200V/S
- 2: 绝缘阻抗不小于100兆欧. Insulation resistance 100M Ω .
- 3: 100%导通OK. Continuity of lead 100% OK.
- 4: 符合ROHS. Rohs COMPLIANT.

9	线上条形码标签 白底黑字	3C0201-01	1	EA
8	纸扎带	4C0016-01	2	EA
7	$\Phi 3.2$ 母圆管端子, 18-22AWG, 磷铜本色 (GEM 98732-PS-0)	2A0246-01	1	EA
6	$\Phi 2.4$ 母圆管端子, 18-22AWG, 磷铜本色 (GEM 98715-PS-0)	2A0241-01	2	EA
5	XR-508 内架, 黑色 (GEM 8732P-3P) insert	2B0064-01	1	EA
4	老鼠尾 (XR-508) IEC-C5 COLOR: 黑色black, PVC 55P	3B0144-01	0.02	Kg
3	法式插头 (XR-323) 16A 250V~, COLOR: 黑色black, PVC 55P	3B0144-01	0.045	Kg
2	$\Phi 4.8$ 法国头端子, 白色, 黄铜镀镍 (德昌 DC-0001A-3)	2A0110-01	1	EA
1	H05VV-F 3G0.75mm ² , COLOR: 黑色black, 裁线长: L=189.5mm.	V10210	1	EA
NO.	DESCRIPTION	Xiongrun PN	QTY	unit

广东雄润电业有限公司
GUANGDONG XIONGRUN ELECTRICAL CO., LTD

DESCRIPTION	DRAW NO.	XR-1638062	UNIT	M M
PARTS NO	SCALE	NONE	DATE	23/07/2019
APPROVED	CHECKED		DRAWING	梁静雅