

Full Specs

Model	35435
Technology	SLA
LCD Resolution	2560 x 1440
Light Source	57 watt parallel LED array
UV Wavelength	405nm
XY Axis Resolution	0.05mm
Z Axis Resolution	0.025mm
Printing Speed	20mm/hour
Maximum Print Size	4.6" x 2.6" x 4.3" (118 x 65 x 110 mm)
Layer Resolution	25 ~ 100 μ m
Interface	Wi-Fi®, microSD™ card
File Format	STL, OBJ

Software	Creation Workshop, Web Slicer, Print Studio, Chitubox 64
Input Power	12 VDC, 5A
AC Adapter Input Power	100 ~ 240 VAC, 50/60 Hz
Dimensions	7.9" x 7.9" x 11.2" (200 x 200 x 285 mm)
Weight	6.6 lbs. (3.0 kg)