

REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------

NOTES1:

UL Standard

1.Rated voltage/current : 300V / 15A

2.Withstanding voltage : AC1600V/1Min.

IEC Standard

Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

1.Dimension shall be interpreted per ASME Y14.5-2009

2.Pitch : 5.0/5.08mm, Poles : N=04~48P

3.Operating temperature: -40°C~+105°C





4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						-	∩	□
To	Over	To	Over	To	Over	To	Over			
6	10	10	24	30	60	100	150			0.1/10
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30			±2'

5.RoHS Compliance

2EDGVHM - 5.0/5.08 - XXP - 1Y - 00A (H)
(Series No.) (Pitch) (Poles) (Single Pitch) (Color):1.(Grey)
(RoHS)
00A-(Standard)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

DETACHED LISTS	PART NO.:	NINGBO DEGSON ELECTRICAL CO., LTD			
	APPD:	NAME:			
	CHKD:	2EDGVHM-5.0/5.08-XXP-1Y-00A(H)			
	DRFT:	TITLE: CUSTOMER DRAWING		REV	DO
	THIRD ANGLE PROJECTION		DRAWING NO.:	SHEET	1/1
		DO NOT SCALE DRAWING	SCALE	1:1	



PCB LAYOUT