

## Jump Starter 12000mAh TX-120

Help for starting the car battery



- Jump Starter
- Lithium-Polymer Akku / Battery 12000mAh
- Laden / Charging
- QC 3.0 Schnellladefunktion / QC 3.0 Quick Charging Function
- Notlicht / Emergency Light
- USB2 QC 3.0 Ausgang / Output: 5V/2.4A & 9V/2A
- USB1 Ausgang / Output: 5V/2.4A
- Hohlstecker 12V/10A / Barrel Connector 12V/10A
- 12V Stromversorgung (Zigarettenanzünder) / 12V Power Supply (cigarette lighter socket)



- 3-in-1 Power Bank: Jump Starter for the car battery, Charging (e.g. Smartphone/Tablet/PC/etc.) & Emergency light
- Jump start: diesel cars up to 2L engine, gasoline/petrol cars up to 4L engine
- Integrated emergency light (3 lighting effects)
- Overcharge and overdischarge protection, fuse & reverse plug protection
- 12000mAh lithium-polymer battery
- QC 3.0 quick charging
- 2x USB outputs for simultaneous charging of two devices
- Power supply via 12V cigarette lighter adapter
- Ideal size to fit into the inner front glove compartment

### Technical Specifications:

- Jump Start output (clamps) 12V for starting a car
- Starting current 200A / Peak current 400A
- Input voltage: at home 15V/1A, 5V/2A, in a car 12V/1A
- Output (USB ports): 5V/2.4A, quick charge (5V/2.4A, 9V/2A), 12V/10A (barrel connector only)
- Input/Output of battery clamps: DC 11.1V–12.6V / 400A
- Built-in rechargeable 12000mAh Li-polymer battery total 11.1V / 41.07Wh (real)
- Battery charging time ~3–6 hours
- Fully charged: can be used ~20 times; charge iPhone X/8 ~5 times & Galaxy S8/S9 ~3.5 times
- Working temperature -10°C up to +40°C
- Weight / Dimensions: 400g / (L) 16.2 x (W) 8.5 x (H) 3.0cm

### Package Contents:

Jump Starter 12000mAh TX-120, Battery clamps with cable, Micro USB charging cable, Cigarette lighter socket with barrel connector, Adapter for the cigarette lighter, Home socket adapter, User Manual



Article-No. 4818

