

Product Datasheet

Product code:	362S
Product type:	High Precision Scissors
Made in:	Italy
Description:	The 362S are high precision scissors with extra fine blades, ideal for miniature work. The Inox material is suitable for cleaning. The blades are hardened to 55HRC hardness.
Tip description:	straight, extra fine
Coating/finishing:	Sandblasted
Body material:	Stainless Steel (Hardened AISI 420)
Picture:	



Product dimensions:	OAL	90.0 mm – 3.543 inch
	Width	45.0 mm – 1.772 inch
	Height	5.0 mm – 0.197 inch
Tip dimensions:	Tip width	0.40 mm – 0.016 inch
	Tip thickness	0.30 mm – 0.012 inch