
TV Safety Notice and Installation Guide

Installation



Installation (Table Top)

Insert Left/Right Stand Base to TV as shown in the picture and fasten them using screws. Note: 1) For Installation on wall, Kindly contact customer care for help. 2) Wall Mount Bracket is not a part of standard accessory.


Turn on the TV

Connect TV's power cord to ac power outlet carefully. Push the power button located at bottom of TV (or press power button on remote.) to turn it on.

Follow screen instructions of quick start guide to setup TV.


Great things are going to happen!


Accessories



1) Accessory Items may vary depending upon model. $2) \ Specifications \ may \ change \ without \ prior \ notice. \ Recommended \ visiting \ website \ \ (www.mi.com) \ for \ latest \ updates.$

• TV interface






This product is qualified for the BEE Star rating in the "home" Mode. The Objectives of Star Labeling Program is designed to promote energy efficient products and practices. When the televivison is initially set up, it is designed to meet the BEE Star Labeling requirements while maintaining optimum picture quality.

- Changes to certain functionalities of this television (TV Guide, Picture/sound etc) may change the power consumption.
- Depending upon such changed setting (eg., Retail mode), the power consumption may vary which possibly could exceed the stated energy consumption. To reset the television to Star rating qualified settings, select "Home" mode from the initial set-up procedure in "factory settings" under the "Set-up" menu.

Using the remote control



- **Power:** Press to select, Reboot, Power Off 20 sec, Delayed Power Off, Screen
- OK: Press to confirm current selection during navigation. You can pause/play the current video during playback, except Live Channels(Set-Top Box or RF).
- **Home:** Short press to quickly return to the Home screen.
- **Direction:** Navigate up/down or left/right through content. During playback use left/right buttons to rewind/fast-forward.
- Back: Go back to the previous level
- Menu: Press to display additional option menu/functions under current watching input. Displays online video search option when at home page. Displays additional video/audio settings while playback. Displays more classification options while external media browsing.

Specs

Basic specs	Screen size: 80CM
•	Screen resolution: HD (1366x768)
	Refresh rate: 60Hz
Hardware specs	CPU: Quad-core CA53
	Internal memory: 1GB DDR
	Flash memory: 8GB eMMC
	Graphics processor: Mali-450MP
Ports	Input interface: HDMI x 3; AV x 1;
	Output interface: Audio output HDMI (ARC) x 1;
	EARPHONE OUT x 1
	Data interface: USB2.0 x 2; Ethernet port x 1

WiFi	2.4GHz (802.11 b/g/n)
Audio and Video Encoding	Audio formats: FLAC; AAC; OGG; DTS- <i>HD</i> Video formats: MPEG 1/2/4; H.263; H.264; H.265; VC1
Model	Model: L32M5-AI

Voltage: 100-240V ~ 50 / 60Hz Power consumption: 50W

Important precautions

- · Place the Mi TV on a smooth, flat surface to avoid the Mi TV falling and causing injury, or damaging the TV.

· Disconnect all cables before moving the Mi TV.

Large Mi TVs need 2 or more people to move safely. Avoid applying pressure to the LED panel
when moving the Mi TV. Avoid shaking the TV or exposing it to excessive vibrations.
 When moving the Mi TV to a new location or to carry out repairs, package the TV using the
original box and packaging materials.

shock, damage, or personal injury:

 When connecting cables, the AC power cord should be unplugged for safety reasons. Be careful not to trip over cables. Before carrying out work or moving the Mi TV, disconnect the AC power cord from the AC

Avoid excessive pinching, bending, modifying, or twisting of the AC power cord, otherwise

. Do not pull the AC power cord when disconnecting the power. • Do not connect too many devices on the same AC power outlet.

Optional items

In case of the following problems ...

The AC power cord is damaged

Any liquid or solid object falls into the case through an outlet.

Usage restrictions

Mi TV may malfunction and cause a fire, electric shock, damage, or personal injury

institution, at an unstable location, next to water, or in a place exposed to rain, moisture, or mildew. If the Mi TV is placed in the dressing room of a public bath or spa, it may be damaged by the sulfide in the air.

with steam or fumes (near a stove or humidifier) to avoid fire, electric shock, or defo Do not boil water, heat, cook noodles, or use mosquito coils near the Mi TV. Do not use the Mi TV when your hands are wet, when the case is open, or with accessories that are

not authorized by the manufacturer. In the case of a lightning storm, disconnect the Mi TV from the AC power cord and AC outlet. Do not install the Mi TV in an open-air location. Failure to follow these conditions may result in personal injury or damage, or cause objects to strike the Mi TV. Damage to Mi TV screen

Operating conditions: nperature: 0°C-45°C Humidity: 20%-80% Storage temperature: -15°C-40°C

Watch TV in appropriate lighting conditions. Watching TV in insufficient light or for long periods can damage your eyesight.

 \bullet The screen and case will get hot when the TV is working. This is normal.

Using and cleaning the screen/case of the Mi TV

Wipe with a soft cloth to remove any dust on the surface of the screen/case. If there is still dust, wipe with a soft cloth that has been moistened with a mild detergent.

 Do not spray water or detergent directly onto the Mi TV. It may drip to the base of the screen

 Do not use scrub pads, alkaline/acid cleaners, scouring powder, or volatile liquids, such as contact with rubber or vinyl products may cause damage to the screen surface and casing materials. It is recommended that you regularly clean the vents to ensure proper ventilation.

This TV displays advertising when it is switched on and off. The advertising that is displayed

1. Lead (Pb) - not over 0.1% by weight;

3. Mercury (Hg) – not over 0.1% by weight;

5. Polybrominated biphenyls (PBBs) - not over 0.1% by weigh

How to dispose this product

e. Wherever possible or as instructed, separate the packaging material according to responsible waste

a. Do not dismantle your electronic Products on your own.
 b. Do not throw electronics in bins having"Do not Dispose"sign.
 c. Do not give e-waste to informal and unorganized sectors like Local Scrap Dealer/ Rag Pickers.

For more accessories, please visit www.mi.com/in Mi Customer Service: www.mi.com/in/service