

medisana®

Design glass scale PS 438

Art. No. 40524 | 40 15588 40524 2

- Invisible LED display only appears during the weighing
- Large easy-to-read LED display (28 mm)
- Convenient „step-on“ switch
- Energy-saving automatic cut-off after 10 seconds



Application | Features

- Invisible LED display (only appears during the weighing)
- Large easy-to-read LED display (28 mm)
- Convenient „step-on“ switch
- Energy-saving automatic cut-off after 10 seconds
- Treads of the standing area made of 6mm safety glass with rounded corners
- Four high-precision strain gauge sensors for accurate readings
- Extra slim design
- Toggles between kg, lb and st
- Overload indication
- Low battery display
- Maximum Capacity: 180 kg, 396lb, 28st4lb
- Incl. batteries: 3 x 1.5V AAA Alkaline

Technical Data

- Dimensions: approx. 30 x 30 x 2.1 cm
- Weight: approx. 1.5 kg
- Display: 7 x 5 cm
- Measuring range: up to 180 kg, 396 lb, 28 st 4 lb
- Graduation: 100 g, 0,2 lb, 1/4 lb
- Batteries: 3 x 1.5V (AAA)

Scope of Delivery

- Design glass scale
- Batteries
- Instruction manual

Logistical data

Sales packaging

1 piece | 30 x 30 x 2.1 cm | 1.5 kg

Packaging unit

4 pieces | 33 x 17.5 x 34 cm | 6.8 kg

05_24SEP2019