



Part No	90NB0LZ3-M07500
Model Name	F512DA-EJ547T
EAN Code	4718017488990
UPC Code	192876488997
LCD Cover Color & Decoration	SLATE GRAY
Top Case Color & Decoration	SLATE GRAY_IMR
On board processor	AMD Quad Core R5-3500U Processor, 2.1 GHz (2M Cache, up to 3.7 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	15.6'//Slim 200nits//FHD 1920x1080 16:9//Anti-Glare//NTSC: 45%
Number Pad	N/A
ScreenPad™	N/A
Chipset	N/A
Memory Slot	1x
Total System Memory	4GB on board + DRAM DDR4 4GB
On board memory	4GB on board
Memory Max.	12G
How to upgrade memory	Upgradable Need to remove bottom/top case
DIMM Memory	DRAM DDR4 4GB
Storage	PCIEG3x2 NVME 512GB M.2 SSD
Expansion Slot(includes used)	DDR4*1 M.2 2280 PCIE G3X2 *1 STD 2.5" SATA HDD *1
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	AMD Radeon™ Vega 8 Graphics
Graphics Feature	N/A
Video memory	N/A
Video Camera	HD Web Camera
FingerPrint	FingerPrint
On board Wireless	N/A
Wireless(Module)	Wi-Fi 5(802.11ac)+Bluetooth 4.1 (Dual band) 1*1
LAN	N/A
Card Reader	Type: Micro SD

USB Port	1x USB 2.0 1x USB3.1 Type A (Gen1) 1x USB3.1 Type C (Gen 1)
Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI
Audio	Sonic Master
Weight (Kg)	1.35 KG (Without Battery) 1.60 KG (with 2 cell battery)
Dimension (cm)	35.7(W) x 23.0(D) x 1.99 ~ 1.99 (H) cm
AC Adapter	ø4.0 45W AC Adapter Output: 19V DC, 2.37A, 45W , Input: 100~240V AC 50/60Hz universal
Battery	37WHrs, 2S1P, 2-cell Li-ion
Replaceable Battery	No
Keyboard type	Chiclet Keyboard
Keyboard Specification	ASUS 348mm keyboard with 19mm full size key pitch, integrated Numeric keypad
Software	ASUS Live Update ASUS GiftBox
Security	N/A
Supplied Accessories	
Warranty	2 years Carry-In Germany and Austria

