



Installation contactor, 230VAC, 2N/O, 25A

Part no. Z-SCH230/1/25-20

Catalog No. 120853

EL-Nummer (Norway) 4100211

Design verification as per IEC/EN 61439

Technical data for design verification				
Rated operational current for specified heat dissipation	I_n	A		25
Heat dissipation per pole, current-dependent	P_{vid}	W		0
Equipment heat dissipation, current-dependent	P_{vid}	W		7.2
Static heat dissipation, non-current-dependent	P_{vs}	W		0
Heat dissipation capacity	P_{diss}	W		0
Operating ambient temperature min.		°C		-40
Operating ambient temperature max.		°C		60
				0

Technical data ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Installation contactor for distribution board (EC001653)				
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Installation contactor for distribution board (ecl@ss10.0.1-27-14-23-08 [AFZ820015])				
Rated operating voltage		V		440 - 440
Rated operation current		A		25
Utility category				1
Rated excitation voltage		V		230 - 230
Voltage type (operating voltage)				AC
Voltage type (excitation voltage)				AC
Number of contacts as normally open contact				2
Number of contacts as normally closed contact				0
Max. incandescent lamp load		W		3000
Max. load fluorescent lamp		VA		1160
Max. load fluorescent lamp (Duo circuit)		VA		2552
Max. load fluorescent lamp (parallel compensated)		VA		1044
Slider for hand switch				No
Number of modular spacings				1
Built-in depth		mm		60
Additional equipment possible				Yes
Degree of protection (IP)				IP40