

KERN EOB 300K100XL



Allround parcel scale with robust stainless steel weighing plate - also with XL platform and large weighing ranges



Power supply

Battery:	4x1.5 V AA
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	CH EURO UK US
Operating time:	60 h

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	1015 x 565 x 85 mm
Gross weight:	18,100 kg
Net weight:	17,100 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	2,700 m
Casing material:	plastic
Dimensions of display device (WxDxH):	235 x 114 x 51 mm
Dimensions of weighing plate (WxDxH):	950 x 500 x 58 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	950 x 500 mm

Piktogramme

STANDARD



OPTION



Measuring system

Adjustment options:	External calibration
Linearity:	200 g
Readability [d]:	100 g
Recommended adjusting weight:	200 kg (M2)
Repeatability:	100 g
Resolution:	3000
Stabilisation time under laboratory conditions:	3 s
Tare range:	300 kg
Warm up time:	10 min
Weighing capacity [Max]:	300 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2,500 cm
-----------------------	----------

Functions

Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C