

KERN HFB 600K200

The professional alternative up to 600 kg with rear-facing second display

KERN®



Display

Additional Display possible:	no
Display digit height:	2,500 cm

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	85 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Battery:	1x12V Type 23A
Charging time:	14 h
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	CH EURO UK
Operating time (Backlight off):	30 h
Operating time (Backlight on):	20 h

Service

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130H
--------------------	----------

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	255 x 435 x 205 mm
Gross weight:	3,200 kg
Net weight:	2,250 kg
Shipping method:	Parcel service
UN number:	2800

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	163 x 126 x 158,5 mm
Dimensions of display device (WxDxH):	163 x 126 x 390 mm
Overall dimensions mounted (WxDxH):	160 x 120 x 395 mm

Measuring system

Adjustment options:	External calibration
Linearity:	400 g
Precision (of [Max]):	0,200 %
Readability [d]:	200 g
Recommended adjusting weight:	600 kg (M3)
Repeatability:	200 g
Resolution:	3000
Stabilisation time under laboratory conditions:	2 s
Tare range:	-600 kg
Warm up time:	10 min
Weighing capacity [Max]:	600 kg
Weighing system:	Strain gauge
Weighing units:	kg lb


KERN HFB 600K200

The professional alternative up to 600 kg with rear-facing second display



Piktogramme

STANDARD



OPTION

