




ARRAY

ALL-PURPOSE ULTRALIGHT RECHARGEABLE HEADLAMP

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
400 lumens	13 hours	80 meters



ARRAY

ALL-PURPOSE ULTRALIGHT RECHARGEABLE HEADLAMP



MARKET APPLICATIONS:

Night running, camping, mountaineering and other outdoors activities.

UPC: 697237812070 0

DESCRIPTION

The Array is an aluminum alloy-made headlamp designed for runners. While offering an incredible 400 lumens output, it is super compact and lightweight. The Array has a light source of two LEDs that provide either independent close-range beam or a close and far mixed beam. The built-in 2000mAh rechargeable Lipo battery is charged with Olight's signature USB magnetic charging cable. The inserted red light-emitting ring of battery pack will be open in synchronization with the headlamp, which is visible in the dark and provides a safety guarantee. The Array is a headlamp that offers convenient and comfort to all users.



FEATURES

- With a brightness of up to 400 lumens and a variety of lighting modes, the Array is ideal for camping, fishing, climbing, and any other adventures that take you out past dark.
- Made of lightweight aluminum alloy material with a super-compact waterproof structure, it is comfortable and adjustable, you may forget you're wearing it.
- The updated magnetic charging cable is super convenient to use, feel free and effortless with this reliable illumination kit by your side.
- The built-in 2000mAh rechargeable Lipo battery supports a runtime up to 13 hours for on-the-go continuous use.
- The smart battery indicators can help to keep you updated of the power status, and automatically enter to taillight mode with blink for safety guarantee in addition.

OUTPUT

SPECIFICATIONS	MODE 1	MODE 2	MODE 3	MODE 4
	400 lumens	200 lumens	100 lumens	50 lumens
	2.5 hours	4.5 hours	6.5 hours	13 hours
	80meters			
	1600cd			

* The above data is the test results using the built-in fully charged 2000mAh3.7V Lipo battery based on ANSI NEMA FL 1-2009 standard under 20°C in windless conditions.

LIGHT SOURCE

High Performance Cool White LED

DIMENSIONS

HEADLAMP:

Length: 1.77in/45mm
Width: 0.91in/23mm
Height: 0.94in/24mm

BATTERY PACK:

Length: 2.54in/64.5mm
Width: 1.67in/42.4mm
Height: 0.72in/24mm

WEIGHT

4.37oz/124g
(Including headband & battery pack)

BODY MATERIAL

Aluminum Alloy (Main body)

POWERED BY

2000mAh 3.7v LiPo Battery

WARRANTY

Olight's 2 Years Warranty
(1 year for the battery pack & charging cable)
Visit: <https://olightworld.com/olight-warranty>

IN THE BOX

Array (Headband&Battery Pack Included) x 1
1.2-meter USB Magnetic Charging Cable x 1
Carrying Case x 1
Cable Clip x 2
Velcro x 1
User Manual x 1

WATERPROOF IPX4



DROP TEST



COMPLIANCE

