


# Warrior X Pro

Superior Tactical Thrower

MAX OUTPUT	MAX RUNTIME	MAX THROW
2,250 lumens	8 hours	600 meters




## MARKET APPLICATIONS

Hunting, search and rescue, law enforcement, etc.

**UPC:** Black 697237812071 7  
Desert Tan 697237812078 6  
OD Green 697237812079 3

## DESCRIPTION

The Warrior X Pro is the upgraded version of Olight's revolutionary Warrior X. Using an updated high discharge 5000mAh 21700 lithium battery, the Warrior X Pro is capable of producing a maximum of 2,250 lumens for up to 600 meters of throw and delivering a 2A current for 100% faster charging than Warrior X. While retaining the classic features of the Warrior X's sturdy, aggressive appearance, as well as the vibration battery indicator, silicone tactical ring and optional magnetic remote switch, the Warrior X Pro features a redesigned raised tail switch for an unprecedented intuitive operation experience. The IPX8-rated aluminum alloy body sports a pronounced knurling pattern for a better grip. With unbeatable performance and indestructible build, the Warrior X Pro is ideal for the professional choice of hunting, search and rescue, or while on duty.



High Performance  
NW LED


Stainless Steel Pocket Clip



New Designed  
Texture Milling

New Designed Raised Magnetic Tail Switch

MCC3 Magnetic Charging Cable



Tactical Grip Ring

## FEATURES

- Using a customized 5000mAh 21700 lithium battery, the Warrior X Pro produces an incredible 2,250-lumen output and 600-meter throw allowing you to see in any harsh situation.
- The redesigned raised tactical tail switch comes with stronger magnetism, and aggressive body knurling for a firmer grip, giving you a simpler interface and operation experience than ever.
- Quickly get back in action with the super-efficient MCC3 charging cable which holds 2A current for 100% doubled faster charging than Warrior X.
- Sturdy Heavy-duty build with a thick IPX8-rated aluminum alloy body, making it tough enough to endure a harsh 3-meter drop test.
- All tactical classics in one: vibration battery indicator, silicone tactical ring, etc. Just feel the sensation of absolute robustness in your hand.

## OUTPUT

SPECIFICATION	Mode 1	Mode 2
	2,250 ± 1,000 ± 300 lumens	300 lumens
	2+100+23 minutes	8 hours
	600 meters	220 meters
	90,000 cd	12,100 cd

### Note:

1. All data above are test results according to ANSI NEMA FL 1-2009 standards.
2. The data above uses the standard 5000mAh 21700 rechargeable battery, and is measured indoors under a room temperature of 25 degrees Celsius with windless conditions.

### WATERPROOF IPX8



### DROP TEST



### COMPLIANCE



## LIGHT SOURCE

High Performance Neutral White LED

## DIMENSIONS

Length: 5.87in/149mm

Head Diameter: 1.54in/39mm

Body Diameter: 1.03in/26.2mm

## WEIGHT

8.43oz/239g (including battery)

## BODY MATERIAL

Aluminum Alloy(main body)

## POWERED BY

Customized 5000mAh 21700 Battery (included)

## WARRANTY

Olight's 5 Years Warranty  
(1 year for the battery&charging cable)  
Visit: <https://olightworld.com/olight-warranty>

## IN THE BOX

Warrior X Pro(Battery Included) x 1  
Stainless Steel Pocket Clip x 1  
MCC3 Magnetic Charging Cable x 1  
Tactical Grip Ring x 1  
Lanyard x 1  
User Manual x 1  
Holster x 1

## OPTIONAL ACCESSORIES

RWX07 Remote Switch(For Rifle)  
RWX Remote Switch(For Shotgun)  
E-WM25 Flashlight-Weapon Mount