



HSM shredstar X6pro - 2 x 15 mm + sep. CD cutting unit



HSM shredstar X6pro document shredder

Reliable and user-friendly particle cut document shredder with the highest security level in the shredstar line. With a separate CD cutting unit for use at the workplace.

Technical data

Order number:	1046111	Intake width:	220 mm
EAN	4026631057776	Container volume / collecting:	20 l
Cutting type:	particle cut	Collection volume in sheets (80 g):	255
Cutting size:	2 x 15 mm	Noise level (idle operation):	ca. 58 dB(A)
Security level (DIN 66399):	E-2 F-2 O-1 P-5 T-2	Weight x Depth x Height:	345 x 245 x 445 mm
Cutting capacity in sheets 80g/m²:	6	Weight:	6,3 kg
Power consumption:	160 W	Shredder material:	Paper, Staples and paper clips, Credit card, CD/DVD
Voltage / Frequency:	220-240 V / 50-60 Hz		

Product information



CDs and DVDs, credit cards and loyalty cards can be easily shredded through the separate CD cutting unit. In the separate CD waste container, the shredded material is separated and is...



The automatic reverse eliminates paper jams and ensures a smooth operation.



The LED indicator shows the device's operating status: Power, Overload, Overheat, Bin full.



Quiet operation

The quiet operating mode minimises noise development at the workplace which is an important consideration for your staff.



Automatic start/stop

The operation is very easy: the device starts automatically when fed paper and automatically stops after shredding is complete.



Filling level indication

The filling level of the waste container can be seen at all times through the inspection window (except HSM shredstar S5).



Effortless emptying

To empty the waste container, the housing top can be easily removed.

