

## ESD Plastic Earth Bonding Boxes



1903EC060



1903EC061



1903EC062



1903EC063

| Item No   | Cable Length (m) | Bonding Point                 | Termination Type |
|-----------|------------------|-------------------------------|------------------|
| 1903EC060 | 3.0              | 3 x Banana Sockets            | M4 Ring Terminal |
| 1903EC061 | 3.0              | 3 x Banana Sockets            | Crocodile Clip   |
| 1903EC062 | 3.0              | 2 x Banana Socket + 10mm Stud | M4 Ring Terminal |
| 1903EC063 | 3.0              | 2 x Banana Socket + 10mm Stud | Crocodile Clip   |

### Specifications:

#### Box

Material: ABS

Dimensions (HxWxD): 37 x 70 x 22 mm

Color: Yellow

Type: Angled

Resistance: 1MΩ

#### Cable

Length: 3.0m

Type: GND

Style: Straight

Diameter: 2.3mm

Diameter of Banana Inputs: 4mm

### Special Note:

Each Earth Contact is protected by a 1MΩ resistor installed behind the Rear cover. If the Workstation ever accidentally become live, the Resistor will limit the Current to less than 0.3mA at 240 volts.

Designed to fit under the front edge of a work bench, rack trolley or other area, within reach of an operator's wrist strap cord or other connecting cords that require grounding. This prevents the bracket from obstructing the work area.