

Shredder Attachment PS 16



(Delivery without basket)

- Strip cut shredder head
- Shredder attachment with extendable arms fits round and rectangular bins 28 – 34 cm wide
- Strip cut shredder, width of the stripes: 6,0 mm
- Security level: P2 (according to DIN 66399)
- Capacity: 6 sheets (A4, 80 g/m²)
- High quality cutting blades made of steel – guarantees a long life
- Motor with over-heating protection
- Mechanical ON/AUTO / OFF / REVERSE switch
- Automatic Start and Stop function by mechanic sensor
- Inlet guide: 220 mm
- Power supply: 220 - 240 V, 50 Hz, 0,9 A, 210 W
- Continuously working time: 2 min
- Dimensions: (WxDxH): 305-380 x 120 x 70 mm
- Weight: net 0,98 kg
- Certificates: CE, RoHS, GS
- Colour: black or white
- Part no.: 2704 (black); 2705 (white)
- EAN: 4030152027040 (black); 4030152027057 (white)
- Packing unit: 6 pcs