

Data Sheet

Built-In Socket including 1 power USB socket, switchable and 1 power socket

Art. Nr. 67326511

22.10.2020

1 Power Double USB Socket switchable

1 Power Socket 21 mm Ø

Input voltage: max. 24 V DC

Current load total: max. 20 A based on a cable cross

section of 2.5 mm²

max. 16 A based on a cable cross

section of 1.5 mm²

Connection: ca. 200mm cable

Power Double USB Socket

Output voltage : 5 V DC

Output current: 4.2 A total (duration)

5 A total (short time)

Current consumption: < 3 mA (idle)

Protection against: Overload, overtemperature,

reverse voltage

Material housing:

Frame: Polycarbonate

Power socket: Polycarbonate / Metal

USB socket: ABS

Switch: Polyamide

Temperature stress: max.110° C



Built-In Socket including 1 power USB socket, switchable and 1 power socket

Art. Nr. 67326511

22.10.2020



