

KERN OBL 137C825



The digital laboratory assistant with infinity optical unit and fixed, pre-centred Koehler illumination



Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OBL-S

Construction

Dimension (W×D×H)	394×185×450 mm
Optical system	Infinity
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Butterfly
Light distribution	20:80

Contrasting methods

Bright field
Darkfield (optional)
Polarisation (optional)
Fluorescent (optional)
Phase contrast (optional)

Standard objectives

4×
10×
40×
100×

Lens quality	Infinity E-Plan
Nosepiece screw-in locations	4
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Colour temperature	6000 K

Functions

Camera - Applicable software	Microscope VIS 2.0 Pro (OXM 902)
Supported operating systems	Win XP
	Win Vista
	Win 7
	Win 8
	Win 10

Interface

Interfaces	USB 2.0
------------	---------

Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Koehler illumination	✓
Filter possible	✓
Field diaphragm	✓

Focussing

Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Condensor

Condensor type	Abbe
----------------	------

Camera

Cameratype	USB2 Microscope camera - C-Mount
Camera - Resolution	5,1 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,5"
Camera - Colour depth	Colour

KERN OBL 137C825



The digital laboratory assistant with infinity optical unit and fixed, pre-centred Koehler illumination

Camera - Framerate	6,8 - 55 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Input voltage power supply / power [Max]	100 - 240 V
Power supply cable removable	removable
Input voltage device / power [Max]	100 - 240 V
Power socket for mains adapter	Power supply cable

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	9 kg
Shipping weight	20,2 kg

Product information

GTIN/EAN number	4045761228665
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

