

KERN OBN 135C832



The digital laboratory assistant with infinity optical unit and professional Koehler illumination



Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OBN-S

Construction

Dimension (W×D×H)	390×200×470 mm
Optical system	Infinity
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Siedentopf
Light distribution	0:100 80:20

Contrasting methods

Bright field
Darkfield (optional)
Polarisation (optional)
Fluorescent (optional)
Phase contrast (optional)

Standard objectives

4×
10×
20×
40×
100×

Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Dioptr adjustment	both-sided
Dioptr adjustment [Min]	-5
Dioptr adjustment [Max]	5
Colour temperature	6000 K

Functions

Camera - Applicable software	Microscope VIS 2.0 Pro (OXM 902)
Supported operating systems	Win XP
	Win Vista
	Win 7
	Win 8
	Win 10

Interface

Interfaces	USB 3.0
------------	---------

Ocular

Ocular field width	HWF
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Koehler illumination	✓
Filter possible	✓
Field diaphragm	✓

Focussing

Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Camera

Cameratype	USB3 Microscope camera - C-Mount
Camera - Resolution	5,1 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,5"
Camera - Colour depth	Colour
Camera - Framerate	14,2 - 101,2 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

KERN OBN 135C832



The digital laboratory assistant with infinity optical unit and professional Koehler illumination

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Input voltage power supply / power [Max]	100 - 240 V
Power supply cable removable	removable
Input voltage device / power [Max]	100 - 240 V
Power socket for mains adapter	Power supply cable

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	14 kg
Shipping weight	20,2 kg

Product information

GTIN/EAN number	4045761228832
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

