

KERN OZL 468C832



The flexible, affordable all-rounder with zoom function as a digital solution for schools, training companies, inspection authorities and laboratories.



Category	
Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OZL-S

Construction	
Dimension (W×D×H)	300×240×490 mm
Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Light distribution	0:100
Contrasting methods	Bright field
Eyepieces fixed	✓
Interpupillary distance [Min]	55 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Functions	
Camera - Applicable software	Microscope VIS 2.0 Pro (OXM 902)
Supported operating systems	Win XP
	Win Vista
	Win 7
	Win 8
	Win 10

Interface	
Interfaces	USB 3.0

Ocular	
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	30 mm

Objective	
Objectives magnifications	0,7x - 4,5x

Illumination	
Illuminance	Transmitted light
Illumination type incident light	LED
Illumination type transmitted light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination dimmable	Incident light + Transmitted light, separate

Focussing	
Field of view [Min]	4,4 mm
Field of view [Max]	28,6 mm
Zoom [Min]	0,7x
Zoom [Max]	4,5x
Sample height [Max]	140 mm
Torque regulation	✓
Working distance	105 mm
Magnification ratio	6,4:1
Focusing mechanism	coarse drive

Stereomicroscope stand	
Stand type	mechanical
Diameter mounting microscope head (Ø)	76 mm

Camera	
Cameratype	USB3 Microscope camera - C-Mount
Camera - Resolution	5,1 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,5"
Camera - Colour depth	Colour
Camera - Framerate	14,2 - 101,2 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

KERN OZL 468C832



The flexible, affordable all-rounder with zoom function as a digital solution for schools, training companies, inspection authorities and laboratories.

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Input voltage power supply / power [Max]	100 - 240 V
Power supply cable removable	removable
Input voltage device / power [Max]	100 - 240 V
Power socket for mains adapter	Power supply cable

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	7 kg
Shipping weight	20,2 kg

Product information

GTIN/EAN number	4045761228863
REACH classification	no prohibited substances

Pictograms

STANDARD

