

KERN OZM 922



Predefined stereo microscope set with simple telescopic arm and 4.5 W ring illumination unit for greater flexibility at the workstation



Category

Brand	Optics
Product category	Microscope
Product group	Stereo microscope set
Product family	OZM-9

Construction

Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Contrasting methods	Bright field
Interpupillary distance [Min]	52 mm
Interpupillary distance [Max]	76 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6

Ocular

Ocular type	Eyepiece HSWF 10x / Ø 23mm with anti-fungus, high eye point
Ocular field width	HSWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	23 mm
Ocular diameter	30 mm

Objective

Objectives magnifications	0,7x - 4,5x
---------------------------	-------------

Illumination

Illuminance	Reflected light
Illumination type incident light	LED
Illumination intensity incident light	4,5 W
Illumination dimmable	Incident light

Focussing

Field of view [Min]	5,1 mm
Field of view [Max]	32,8 mm
Standard total magnification [Min]	7x
Standard total magnification [Max]	45x
Zoom [Min]	0,7x
Zoom [Max]	4,5x
Sample height [Max]	130 mm
Torque regulation	✓
Working distance	110 mm
Magnification ratio	6,4:1
Focusing mechanism	coarse drive

Stereomicroscope stand

Stand type	universal (ball-bearing double telescopic arm with plate)
Diameter mounting universal stand (Ø)	32 mm
Diameter mounting microscope head (Ø)	76 mm

Power Supply

Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V
Power socket for mains adapter	Protective contact plug

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

KERN OZM 922



Predefined stereo microscope set with simple telescopic arm and 4.5 W ring illumination unit for greater flexibility at the workstation

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	700×520×350 mm
Shipping method	Parcel service
Net weight approx.	22 kg
Gross weight approx.	24 kg
Shipping weight	25,5 kg

Product information

GTIN/EAN number	4045761218376
REACH classification	no prohibited substances

Pictograms

STANDARD

