

# KERN 326-056



Weight set, F1, 1 g - 500 g, Eco Shape, stainless steel polished, in aluminium case



## Category

|                  |            |
|------------------|------------|
| Brand            | KERN       |
| Product category | Weight set |
| Product group    | OIML F1    |
| Product family   | 326        |

## Measuring System

|                             |             |
|-----------------------------|-------------|
| Weight OIML class           | F1          |
| Test weight - nominal value | 1 g - 500 g |
| OIML-compliant              | ✓           |

## Construction

|                    |                          |
|--------------------|--------------------------|
| Dimension (W×D×H)  | 210×140×98 mm            |
| Shape weight       | Eco Shape                |
| Material           | stainless steel polished |
| Case of weight set | in aluminium case        |

## Services (optional)

|                                              |         |
|----------------------------------------------|---------|
| Article number for DAkkS calibration         | 962-418 |
| Article number for guaranteed plus-deviation | 921-418 |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 210×140×98 mm  |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,75 kg        |
| Gross weight approx.         | 2,0 kg         |
| Shipping weight              | 2 kg           |

## Optional cases

|                                 |             |
|---------------------------------|-------------|
| Case - Aluminium article number | 314-050-600 |
|---------------------------------|-------------|

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761224117            |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD



### OPTION

