

SAUTER CO 2000-Y2

Miniature cylindrical load cell made from stainless steel

KERN



Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Combined error	0,5%
Temperature coefficient - characteristic value	± 0.05% F.S. / 10 °C
Zero balance	≤± 1.0%FS
Temperature coefficient - zero signal	± 0.05% F.S. / 10 °C
Creep error (30 minutes)	+/- 0.1%FS
Safe overload	150%
Ultimate overload	200%

Functions

IP protection - complete device	IP65
---------------------------------	------

Construction

Material	steel, stainless
Design	Tension-/compression rod
Dimension (Ø×H)	51×75 mm
Cable length	2 m
Mounting - force application	External thread M12
Mounting - force dissipation	External thread M12

Environmental conditions

Use temperature [Min]	0 °C
Use temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration (tensile force)	961-164V
Article number for factory calibration (tensile force/ compressive force)	961-364V

Product information

GTIN/EAN number	4045761233034
REACH classification	no prohibited substances

Packing & Shipping

Shipping method	Parcel service
Delivery time	1 d

Category	
Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CO Y2

Measuring System	
Weighing capacity [Max]	2000 kg
Measuring range force [Max] (N)	20 kN
Load cell - characteristic value - nominal	1,5 mV/V
Load cell OIML class	G5
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Measuring applications	force mass
Directions of force	tension compression
Load cell - Input resistance - nominal	350 Ω
Load cell - Input resistance - variance	20 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Output resistance - variance	3 Ω
Load cell - Recommended excitation voltage [Min]	9 V

SAUTER CO 2000-Y2



Miniature cylindrical load cell made from stainless steel

Dimensions packaging (W×D×H)	120×90×85 mm
------------------------------	--------------

Net weight approx.	0,55 kg
--------------------	---------

Gross weight approx.	0,60 kg
----------------------	---------

Shipping weight	0,562 kg
-----------------	----------

Pictograms

STANDARD



OPTION

