

ACTIVE DIFFERENTIAL PROBES SERIES 8000

The new TT-SI 8010A and TT-SI 8010B active differential probes allow safe, accurate high voltage measurements between two voltage points where neither point is referenced to ground. These two probes are perfect designed for a wide variety of measurements up to 100MHz / $\pm 7000V$ and are compatible with oscilloscopes from all major manufacturers.



	TT-SI 8010A	TT-SI 8010B
Order Number	15411	15412
Bandwidth	70MHz	100MHz
Attenuation	x100 / x1000	
DC-Accuracy	$\pm 2\%$	
Max. Input Voltage Differential Mode	$\pm 700V$ (DC + AC peak) @ x10 $\pm 7000V$ (DC + AC peak) @ x100	
Max. Input Voltage Common Mode	$\pm 7000V$ (DC + peak AC)	
Maximum Input Voltage (each side to ground)	1000Vrms CAT III 2300Vrms	
Safety Standard	IEC1010-031:2015	
Supplied Accessories	2 x Test Leads with insulated 4mm Banana Plugs (red & black) 2 x Grabber (red & black), 2 x Pincer (red & black) 2 x Alligator Clips (red & black), 1 x Insulated BNC Cable, 100cm 1 x USB power lead, 1 x Mains Adapter 220V EU Version	