


No.	Changes and/or Note No.	Date	Intr.	No.	Changes and/or Note No.	Date	Intr.



SPECIFICATION

MATERIAL

WIRE :PVC WIRE COMPOUND UL1007
CASE: ABS PA-707 NATURE CHROMIUM COATING
Insulator: P.B.T & Glass fill reinforced UL94V-0
Contacts: Brass(standard);Phosphor Bronze(choose)
Shell: ABS UL94HB Finished Metalized

Rivet,Boardlock: Brass

CONTACT PLATING

Underplate: 50m" Nickel

Contact area: 1m" Selective Gold

ELECTRICAL CHARACTERISTICS

Operation voltage: 250 VAC max.

Current rating: 3 Amps max.

Contact resistance: 15 mohms max.


Insulation resistance: 3000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -55, C TO +105, C

WIRE SPECIFICATION COUNT		
BLACK	M-F	2
BROWN	F-F	2
RED	M-F	2
ORANGE	M-F	2
YELLOW	M-F	2
GREEN	M-F	1
BLUE	M-F	1
VIOLET	M-F	1
GRAY	M-F	1
WHITE	M-F	1

PARTS OPTION



DATE	DRAWN	SCALE	MATERIAL TYPE
	APPROVED		REPLACES
15-way Male to 15-way Female GA-1515-MF-M-K			DRAWING No 2111-0105-12