D-Sub

TECHNICAL SPECIFICATIONS

Materials:

Unshielded Hood: UL-recognised plastic material


Colour: Black

Shielded Hood: UL-recognised plastic material

Plating: Nickel over Copper


Operating Temperature: -30°C to +110°C


Jackscrews: UNC 4-40 (Standard)



Features:

- Suitable for sizes 9, 15, 25
- Snap-Lock system
- Available in EMI-shielded and unshielded version
- Delivered complete with wires and Sub-D
- Re-openable
- Also available in Unshielded version
- · Pre-wired connectors on request
- · Also available without wire kit + connector





| Size DA | Dim A | Dim B | Dim C |
|---------|-------|-------|-------|
| 9-way | 33,0 | 15,0 | 49,5 |
| 15-way | 41,3 | 15,0 | 39,0 |
| 25-way | 55,1 | 15,0 | 39,0 |

Ordering information: Unshielded Version

| Size: | P/N - Kitted: | Product Code: |
|--------|---------------|----------------|
| 9-way | 2112-0100-01 | DA09-SMJ6-K-RC |
| 25-way | 2112-0100-03 | DA25-SMJ6-K-RC |
| | | |
| 9-way | 2112-0100-11 | DA09-PMJ6-K-RC |
| 25-way | 2112-0100-13 | DA25-PMJ6-K-RC |
| | | |
| 9-way | 2112-0101-01 | DA09-SMJ8-K-RC |
| 25-way | 2112-0101-03 | DA25-SMJ8-K-RC |
| | | |
| 9-way | 2112-0101-11 | DA09-PMJ8-K-RC |
| 25-way | 2112-0101-13 | DA25-PMJ8-K-RC |

Ordering information:

Shielded Version

| Size: | P/N - Kitted: | Product Code: |
|--------|---------------|------------------|
| 9-way | 2112-0105-01 | DA09-SMJ8-M-K-RC |
| 25-way | 2112-0105-03 | DA25-SMJ8-M-K-RC |
| | | |
| 9-way | 2112-0105-11 | DA09-PMJ8-M-K-RC |
| 25-way | 2112-0105-13 | DA25-PMJ8-M-K-RC |

SMJ6 = Sub-D Female to RJ11

PMJ6 = Sub-D Male to RJ11

SMJ8 = Sub-D Female to RJ45

PMJ8 = Sub-D Male to RJ45



Tel: +46-(0)35-15 13 90 e-mail: connectors@encitech.com

