KERN **OZB-A4516**

Double gooseneck illumination for best illumination of your sample



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Microscope illumination
Product family	OZB-IF

Construction	
Dimension (W×D×H)	100×200×150 mm
Gooseneck length	540 mm
Beleuchtungsart	LED
Illuminance	20 W
Colour temperature	6400 K
Illumination dimmable	✓

Power Supply	
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Power supply – Cable length	2,5 m

Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval	
CE mark	✓

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	300×250×250 mm
Shipping method	Parcel service
Net weight approx.	3,8 kg
Gross weight approx.	4,0 kg
Shipping weight	4 kg

Product information	
GTIN/EAN number	4045761217720
REACH classification	no prohibited substances

Pictograms

STANDARD

