

KERN 327-04

KERN

Individual weight, OIML Class F1, 10 g, Knob, stainless steel polished



Article number for guaranteed plus-deviation 921-434

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	10×10×19 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Optional cases

Case - Plastic article number	347-050-400
Case - Aluminium article number	317-040-600
Case - Wood article number	317-040-100

Product information

GTIN/EAN number	4045761004719
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	327

Measuring System

Test weight - volume (cm ³)	1,25
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m ³)	140
Test weight - volume uncertainty (cm ³)	0,0156
Weight OIML class	F1
Test weight - nominal value	10 g
Permissible tolerance according to OIML (+/-)	0,2 mg
Test weight - Density (kg/m ³)	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	6000
Test weight - Density [Max] (OIML)	12000

Construction

Shape weight	Knob
Dimensions (Ø×H)	10×19 mm
Material	stainless steel polished
Adjustment method	Adjusting cavity - screwed

Services (optional)

Article number for DAkkS calibration	962-434
--------------------------------------	---------